

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Random Orbit Sander

PRO GEX 34-150



Robust 150mm random orbit sander with high removal rate

The most important data

| | |
|----------------------|--------|
| Rated input power | 340 W |
| Sanding pad diameter | 150 mm |
| Orbit diameter | 4 mm |

Part Number 0 601 372 860

Technical data

Technical data

| | |
|--|--------------------|
| Sanding pad diameter | 150 mm |
| No-load speed | 4,500 – 12,000 rpm |
| Orbital stroke rate | 9,000 – 24,000 opm |
| Eccentricity | 2 mm |
| Rated input power | 340 W |
| Weight | 2.1 kg |
| Orbit diameter | 4 mm |
| Packaging dimensions (width x length x height) | 167 x 354 x 213 mm |
| Voltage, electrical | 110 V |

Noise/vibration information

Sanding solid wood

| | |
|-----------------------------|----------------------|
| Vibration emission value ah | 5 m/s ² |
| Uncertainty K | 1.5 m/s ² |



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Constant speed and high removal rate for efficient results even on demanding surfaces
- Aluminium bearing flange ensures a long tool lifetime and makes it ideal for use on tough applications
- Multi-hole sanding pad for sanding sheets with different hole pattern and for significantly increased dust extraction

**HEAVY
DUTY**



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

