




LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			AD2	REVISED PER ECO-11-004820	11MAR11	RK	HMR




15 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

1-641119-7	SUPERSEDED BY 4-641119-7
1-641119-8	SUPERSEDED BY 4-641119-8
1-641119-9	SUPERSEDED BY 4-641119-9
2-641119-1	SUPERSEDED BY 5-641119-1
2-641119-2	SUPERSEDED BY 5-641119-2
2-641119-3	SUPERSEDED BY 5-641119-3

LEAD FREE	95.10	[3.744]	24	5-641119-4
	91.14	[3.588]	23	5-641119-3
	87.17	[3.432]	22	5-641119-2
	83.21	[3.276]	21	5-641119-1
	79.25	[3.120]	20	5-641119-0
	75.29	[2.964]	19	4-641119-9
	71.32	[2.808]	18	4-641119-8
	67.36	[2.652]	17	4-641119-7
	63.40	[2.496]	16	4-641119-6
	59.44	[2.340]	15	4-641119-5
	55.47	[2.184]	14	4-641119-4
	51.51	[2.028]	13	4-641119-3
	47.55	[1.872]	12	4-641119-2
	43.59	[1.716]	11	4-641119-1
	39.62	[1.560]	10	4-641119-0
	35.66	[1.404]	9	3-641119-9
	31.70	[1.248]	8	3-641119-8
	27.74	[1.092]	7	3-641119-7
	23.77	[.936]	6	3-641119-6
	19.81	[.780]	5	3-641119-5
	15.85	[.624]	4	3-641119-4
	11.89	[.468]	3	3-641119-3
	7.92	[.312]	2	3-641119-2
	DIM (L)		NO.OF POSN	ASSEMBLY

CONTAINS LEAD	95.10	[3.744]	24	2-641119-4
	91.14	[3.588]	23	2-641119-3 
	87.17	[3.432]	22	2-641119-2 
	83.21	[3.276]	21	2-641119-1 
	79.25	[3.120]	20	2-641119-0
	75.29	[2.964]	19	1-641119-9 
	71.32	[2.808]	18	1-641119-8 
	67.36	[2.652]	17	1-641119-7 
	63.40	[2.496]	16	1-641119-6
	59.44	[2.340]	15	1-641119-5
	55.47	[2.184]	14	1-641119-4
	51.51	[2.028]	13	1-641119-3
	47.55	[1.872]	12	1-641119-2
	43.59	[1.716]	11	1-641119-1
	39.62	[1.560]	10	1-641119-0
	35.66	[1.404]	9	641119-9
	31.70	[1.248]	8	641119-8
	27.74	[1.092]	7	641119-7
	23.77	[.936]	6	641119-6
	19.81	[.780]	5	641119-5
	15.85	[.624]	4	641119-4
	11.89	[.468]	3	641119-3
	7.92	[.312]	2	641119-2
		DIM (L)	NO.OF POSN	ASSEMBLY

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN S. HOOVER 07-NOV-2002 OK D. BOSSI 07-NOV-2002 APPROVED D. BOSSI 07-NOV-2002		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 0.13 [0.005] 2 PLC ± 3 PLC ± 4 PLC ± ANGLES FINISH ±		NAME MTA-156 HEADER ASSEMBLY, FRICTION LOCK, STRAIGHT, .045 SQUARE POST, .000015 GOLD	
MATERIAL 		APPLICATION SPEC WEIGHT		SIZE A1	
		CUSTOMER DRAWING		DRAWING NO 00779	
				SCALE 5:1	
				SHEET 1 of 1	
				REV. AD	