

Relays & Contactors > Electromechanical Relays

Relay & Contactor Type: **General Purpose Power Relay**Coil Magnetic System: **Non-Polarized, Monostable**Contact Arrangement: **3 Form X 3PST-NO-DM**Current Type: **DC**Contact Current Rating: **35 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Power Relay
------------------------	-----------------------------

Configuration Features

Coil Special Features	Coil Suppression Diode
Relay Options	Back EMF Suppression
Contact Arrangement	3 Form X 3PST-NO-DM

Electrical Characteristics

Coil Resistance	160 Ω
Contact Switching Voltage (Max)	115 VAC, 200 VAC
Contact Current Rating	35 A
Coil Voltage Rating	28 VDC

Body Features

Enclosure Type	Hermetically Sealed
----------------	---------------------

Contact Features

Contact Material	Silver Cadmium Oxide
Terminal Plating	Tin-Lead

Termination Features

Main Termination & Connection Type	Solder Hook Terminals
------------------------------------	-----------------------

Coil Termination & Connection Type

Solder Hook Terminals

Mechanical Attachment

Product Mounting Feature Type

Mounting Studs

Product Mount Type

Panel Mount

Usage Conditions

Operating Temperature Range

-70 – 125 °C[-94 – 257 °F]

Environmental Ambient Temperature (Max)

125 °C[257 °F]

Operation/Application

Vibration Resistance

10G's, 5 – 1000Hz

Shock Resistance

50G's, 11ms

Coil Magnetic System

Non-Polarized, Monostable

Current Type

DC

Other

Contact Current Class

>32 – ≤50 A

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Not Compliant

EU ELV Directive 2000/53/EC

Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)

Candidate List Declared Against: JAN 2025 (247)

SVHC > Threshold:

Cd (10% in Component Part)

Cadmium oxide (7.84% in M-15215-1)

Pb (.13% in M-15215-2)

Article Safe Usage Statements:

Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent

chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 2-1617749-2
FCA-210-1024M=M83536/10-024M



TE Part # 3-1617806-7
FC-325-1=MS27418-1A


Also in the Series | CII FC-335



AC Relays(4)



DC Relays(4)



Electromechanical Relays(8)

Customers Also Bought



TE Part #02291333-000
LDM-1000 LVDT CONDITIONER DIN




TE Part #ZPF00000000100794
DMC-MD 20 C



TE Part #CTJ-3D-03
RAIL ASSY



TE Part #CX2097-000
D-150-C-13



TE Part #796693-3
3 POS TERMI-BLOK PLUG STACK



TE Part #2-1617798-7
FCAC-150-KR4



TE Part #2176247-8
TJJ 150W 15R 5%



TE Part #5745583-1
UNIV SLIDLATCH KIT SZ 2

Documents

Product Drawings

[FC-335-CW4=RELAY, 3PST](#)

English

Datasheets & Catalog Pages

[CII FC-335 Series Relay](#)

English