




Industrial RJ45 Mag Jack

TE Internal #: 5-2337995-1

RJ45 with Integrated Magnetics Connector, Multiple Ports, 2 x 1, Jack, Shielded, Cat 5, Inverted (Top) / Standard (Bottom), Industrial RJ45 Mag Jack

[View on TE.com >](#)

Connectors > Modular Jacks & Plugs > RJ45 Connectors



Modular Jack & Plug Interface Type: **RJ45 with Integrated Magnetics**

Port Configuration: **Multiple Ports**

Port Matrix Configuration: **2 x 1**

Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**

Connector Contact Density: **Standard**

Features

Product Type Features

Modular Jack & Plug Interface Type	RJ45 with Integrated Magnetics
Modular Jacks & Plugs Products	RJ Type Jacks & Plugs
Modular Connector Style	Jack
Grounding Options	PCB and Panel Ground
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of PCB Ground Tabs	6
Panel Ground Location	Top and Side
Number of Panel Ground Tabs	10
Multiple Port Configuration	Stacked
Port Configuration	Multiple Ports
Port Matrix Configuration	2 x 1
Connector Contact Density	Standard
Number of Positions	8



Number of Loaded Positions	8
----------------------------	---

PCB Mount Orientation	Right Angle
-----------------------	-------------

Signal Characteristics

Data Rate	10 Mb/s, 100 Mb/s
-----------	-------------------

Body Features

LED Color (Bottom Left)	Green
-------------------------	-------

Insulator Material	LCP
--------------------	-----

LED Color (Bottom Right)	Yellow
--------------------------	--------

Shield Plating Material	Nickel
-------------------------	--------

Shield Plating Finish	Matte
-----------------------	-------

Shield Material	Brass
-----------------	-------

PCB Retention Feature Material	LCP
--------------------------------	-----

LED Color (Top Right)	Yellow
-----------------------	--------

LED Color (Top Left)	Green
----------------------	-------

PCB Ground Tab Location	11.43 mm, 15.49 mm, -4.57 mm[-.18 in][.45 in][.61 in]
-------------------------	---

Modular Jack Latch Orientation	Inverted (Top) / Standard (Bottom)
--------------------------------	------------------------------------

Connector Profile	Standard
-------------------	----------

Contact Features

Contact Underplating Material	Nickel
-------------------------------	--------

PCB Contact Termination Area Plating Material Finish	Matte
--	-------

PCB Contact Termination Area Plating Material	Tin
---	-----

Contact Mating Area Plating Material	Gold (Au)
--------------------------------------	-----------

Contact Base Material	Copper Alloy
-----------------------	--------------

Contact Mating Area Plating Material Thickness	.76 μm[30 μin]
--	----------------

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

PCB Mount Retention Type	Boardlock
--------------------------	-----------

Housing Features

Mating Entry Location	Side
-----------------------	------

Housing Color	Black
---------------	-------

--	--



Housing Material	LCP (Liquid Crystal Polymer)
------------------	------------------------------

Dimensions

Connector Height	25.55 mm[1.006 in]
------------------	--------------------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Indicator Type	LED
Shielded	Yes

Industry Standards

UL Flammability Rating	UL 94V-0
Performance Category	Cat 5

Packaging Features

Packaging Quantity	40
Packaging Method	Tray

Other

Shield Panel Ground Type	Shield has bottom panel grounds.
--------------------------	----------------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1987236-1

RJ45 CONNECTOR IP20 45 DEG., INDUSTRIAL

Also in the Series | Industrial RJ45 Mag Jack



RJ45 Connectors(102)

Customers Also Bought

TE Part #178326-3

DYNAMIC DBL ROW HDR ASSY 12P V

TE Part #4-2176316-8

MELF SMA\_A 680R 1% 50PPM 0207 1W



TE Part #114712-E  
MICROSTV 12 407 188 \* 0007 J 3 114712

TE Part #225693-E  
POWELM BUCHSE ZWEIM M3 5 2,54 \* EP 6 CUS

TE Part #1462042-9  
IMC06CGR=IM Relay 140mW 12V 1CO EP 6 CUS

TE Part #1-1393230-1  
RP3SL024

TE Part #4-2176237-0  
CPF A 0603 6K2 0.1% 25PPM 5K RL

TE Part #234206-E  
SMCQ 12 M AB VV 8-23 CL \* H007 137 E005

Documents

Product Drawings

RJ45 JACK MAG. POE 10/100 LED 2X1

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_5-2337995-1\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_5-2337995-1\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_5-2337995-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ETHERNET JACKS WITH INTEGRATED MAGNETICS AND PoE

English

Product Specifications

Application Specification

English