



M12 FUEL™

M12 FIR38G2-252B

M12 FUEL™ 3/8" RATCHET

With up to 95 Nm of max torque and 400 rpm's, this ratchet offers the perfect combination of power and speed for the most demanding applications

19 mm low profile head design allows users better access in tight spaces

Tool body is ergonomically optimised to fit comfortably in the hand

Different and interchangeable trigger designs allow the ratchet to be customised to personal preferences

Maximum control and precession for every application thanks to the variable speed metal trigger

Industry leading FUEL™ technology combined with a robust design for greater durability

Premium rubber overmold withstands corrosive materials and provides increased comfort when in use

The LED light illuminates the work area while the on-board fuel gauge displays remaining run time

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M12™ batteries



REDLITHIUM™



	M12 FIR38G2-0	M12 FIR38G2-252B
Head profile [mm]	19	
19	Length (mm)	
303	303	
Weight with battery pack (EPTA) (kg)	0.9 (M12 HB2.5)	
0.9 (M12 HB2.5)	Kit included	
No batteries supplied, No charger supplied, No kitbox or bag supplied	2 x M12 HB2.5 Battery pack, C12 C Charger, Tool bag	
Article number	4933498936	
4933498937	SSP Excl. VAT_Print [Text] [£]	