



Part Number : [1200980104](#)

Product Description : Micro-Change (M12) Single-Ended Cordset, 5 Poles, B-Coded, Male (Straight) to Pigtail, 24 AWG, 5.0m (16.40') Length, PROFIBUS PUR Cable Preferred Version in Europe

Series Number : 120098

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : B05S06PP4M050

Documents & Resources

Drawings

[1200980104_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120098
Description	Micro-Change (M12) Single-Ended Cordset, 5 Poles, B-Coded, Male (Straight) to Pigtail, 24 AWG, 5.0m (16.40') Length, PROFIBUS PUR Cable Preferred Version in Europe
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	EtherNet
Type	Single Ended
UPC	78678850770

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC/DC

Physical

Cable Diameter	8.00mm (.315")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Violet
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded

Gender	Male-Pigtail
Keyway	B-Coded
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	402.693/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Twisted Pair
Wire Size (AWG)	24