XS4P18AB120M12

Inductive proximity sensors XS, inductive sensor XS4 M18, L40.6 mm, PBT, Sn8mm, 12...24 VDC, M12



Main

Range of product	Telemecanique Inductive proximity sensors XS
Series name	Application
Sensor type	Inductive proximity sensor
Electrical circuit type	Analog output
Sensor name	XS4
Sensor design	Cylindrical M18
Size	41 mm
Body type	Fixed
Detector flush mounting acceptance	Non flush mountable
Material	Plastic
Type of output signal	Analogue
Wiring technique	2-wire
[Sn] nominal sensing distance	8 mm
Output circuit type	DC
Analogue output range	420 mA
Electrical connection	Male connector M12, 4 pins
[Us] rated supply voltage	1224 V DC
IP degree of protection	IP67 conforming to IEC 60529

Complementary

Complementary	
Thread type	M18 x 1
Detection face	Frontal
Front material	PPS
Enclosure material	PBT
Operating zone	0.88 mm
Repeat accuracy	<= 3% of Sr
Linearity error	+/- 2 mA
Supply voltage limits	1038 V DC
Switching frequency	<= 500 Hz
Current consumption	4 mA no-load
Maximum output current drift	10 %
Marking	CE
Threaded length	26 mm
Height	18 mm
Length	41 mm

Environment

Product certifications	CSA[RETURN]UL
Ambient air temperature for operation	-2570 °C

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	4.1 cm	
Package 1 Width	9.5 cm	
Package 1 Length	13 cm	
Package 1 Weight	97 g	

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	☑ End of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

