

Europe connectors - EC 10 TR - 3240178


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Polyamide Europe terminal strip, transparent, for connecting solid conductors and stranded conductors with ferrules with a cross section of 1 to 10 mm²



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 457835
GTIN	4046356457835
Weight per Piece (excluding packing)	44.480 g
Custom tariff number	85369010
Country of origin	Austria
Note	Made to Order (non-returnable)

Technical data

General

Number of positions	12
Number of levels	1
Number of connections	24
Nominal cross section	10 mm ²
Color	transparent
Insulating material	PA
Flammability rating according to UL 94	V2
Ambient temperature (operation)	-40 °C ... 110 °C
Maximum load current	57 A (with 10 mm ² conductor cross section)
Nominal current I _N	57 A (with 10 mm ² conductor cross section)
Nominal voltage U _N	450 V (Only use up to 250 V without securing.)
Open side panel	No

Europe connectors - EC 10 TR - 3240178

Technical data

Dimensions

Width	22.2 mm
Length	132.7 mm
Height	17.3 mm
Depth	22.2 mm
Drill hole spacing	11.5 mm
Pitch	11.5 mm

Connection data

Connection method	Screw connection
Conductor cross section solid min.	1 mm ²
Conductor cross section solid max.	10 mm ²
Conductor cross section AWG min.	16
Conductor cross section AWG max.	8
Conductor cross section flexible min.	1 mm ²
Conductor cross section flexible max.	10 mm ²
Min. AWG conductor cross section, flexible	16
Max. AWG conductor cross section, flexible	8
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.75 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.75 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	4 mm ²
2 conductors with same cross section, solid min.	0.75 mm ²
2 conductors with same cross section, solid max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.75 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²
Stripping length	7 mm
Screw thread	M3,5
Tightening torque, min	0.8 Nm
Tightening torque max	1 Nm

Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V2

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Europe connectors - EC 10 TR - 3240178

Classifications

eCl@ss

eCl@ss 4.0	27141106
eCl@ss 4.1	27141106
eCl@ss 5.0	27141106
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141106
eCl@ss 8.0	27141106
eCl@ss 9.0	27141106

ETIM

ETIM 3.0	EC001284
ETIM 4.0	EC001284
ETIM 5.0	EC001284
ETIM 6.0	EC001284

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	39121409

Approvals


Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
	D	B	C
Nominal voltage UN	300 V	300 V	300 V
Nominal current IN	50 A	50 A	50 A
mm ² /AWG/kcmil	14-8	14-8	14-8

Europe connectors - EC 10 TR - 3240178

Approvals

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
----------------	--	---	--------------

	D	B	C
Nominal voltage UN	300 V	300 V	300 V
Nominal current IN	50 A	50 A	50 A
mm ² /AWG/kcmil	14-8	14-8	14-8

EAC		RU C- DE.AI30.B.01102
-----	--	--------------------------

cULus Recognized	
------------------	--