



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (13% in 4690971273) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-104118-4
60 SYSTEM 50 HDR DRRA UNSHRD




TE Part # 1-103916-4
60 SYSTEM 50 HDR DRST UNSHRD



TE Part # 104069-7
60 SYSTEM 50 HDR DRRA SHRD




TE Part # 104068-6
60 SYSTEM 50 HDR DRST SHRD




TE Part # 104549-8
60 SYS50 SURFMNT HDR DRST SHRD



TE Part # 104477-9
60 SYSTEM 50 HDR DRRA SHRD



TE Part # 147377-6
60 SYS50 SMT HDR DR SHD W/O HD




TE Part # 104864-1
60 SYSTEM 50 HDR DRST SHRD



TE Part # 104666-7
60 SYSTEM 50 HDR DRST SHRD


Customers Also Bought



TE Part #6-1437213-1
FSK-23A-12



TE Part #87247-7
07 MODI HDR SRST .156CL




TE Part #352332-1
2MM HM TYPE A MALE HDR 154 POS



TE Part #3-535512-8
84 MODII HORZ DR CE EESS .100



TE Part #4-1617351-2
JM5C-5XM=M39016/11-033M



TE Part #1-532825-4
HDI RECP ASSY 2 ROW 150 POS



TE Part #2102429-4
Pin Assy, 320 Psn, LF, 30 AU, Mezalok



TE Part #ES2050402BGM
ES2050402BGM=RELAY



TE Part #2102539-1 ASSY, RECPT SHELL, SKT INSERT, PCB KEY N	TE Part #2102644-1 Assy, recpt shell, pin insert, PCB Key N
--	--

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_104550-7_S.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_104550-7_S.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_104550-7_S.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English