

3NA3220 LV HRC FUSE LINK 500V S.2 50A

As of 2012-03-02

LV HRC FUSE LINK GL/GG WITH NON-INSULATED GRIP LUGS WITH FRONT INDICATOR SIZE 2, 50A, AC 500V/DC 440V



Similar to image

Technical data:



Current / for AC / rated value	A	50
Operating class of the fuse link		gG
Size of the fallback-system / acc. to DIN EN 60269-1		NH2
Supply voltage		
<ul style="list-style-type: none"> for AC / rated value 	V	500
<ul style="list-style-type: none"> for DC 	V	440
Switching capacity current		
<ul style="list-style-type: none"> in accordance with IEC 60947-2 / rated value 	kA	120
<ul style="list-style-type: none"> with DC / in accordance with IEC 60947-2 / rated value 	kA	25
Design of an identification indicator		Front indicators
Ambient temperature		
<ul style="list-style-type: none"> minimum 	°C	-5
<ul style="list-style-type: none"> maximum 	°C	40

Certificates/approvals:

General Product Approval	Declaration of Conformity	Test Certificates	Shipping Approval	other
<input checked="" type="checkbox"/> KEMA	ROSTEST Manufacturer	Manufacturer	<input checked="" type="checkbox"/> GL (Germanischer Lloyd)	Manufacturer

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)



last change:

Aug 26, 2011