



Technical data

NATV12LL/3AS

Roller follower with inner ring



VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	12 mm
D - External diameter	32 mm
C - Width of bearing, drawn cup or outer ring	14 mm
F - Under roller diameter	17 mm
B - Bearing/Inner ring width	15 mm
e - Inlet diameter of roller or washer	25 mm
R - Track roller radius	500 mm
Bearing with/without cage	Sans



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

Radial clearance class	CN
Precision class	P0
Mass	0,074 kg

PRODUCT PERFORMANCE

Cr - Dynamic load rating	13 kN
C0r - Static load rating	23 kN
Track load capacity spherical outer ring	2,86 kN
N lim - Grease lubrication limit speed	6000 tr/min
Tmin - Min operating temperature	-20 °C
Tmax - Max operating temperature	100 °C

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	NATV12LL/3AS
Image	NRBNATV_LL_1.jpg, NRBNATV_LL_3.jpg
Rolling element material	Acier 100Cr6

