


HBL5656




Nickel plated brass flange, brown phenolic housing (mounting screws packaged separately).

Product Specifications

Device Type	Flanged Receptacle
Standard	NEMA
Amperage	15A
Voltage	250V
Poles and Wires	2 Pole, 3 Wire Grounding
Wiring Method	Side Wire Only
Hospital Grade ?	No
Receptacle Grade	Heavy Duty Spec Grade
Face Style	Finder Groove
Flange Style	Standard Metallic
Color	 Brown
NEMA No.	6-15R
Horsepower	1.5
Description	Heavy Duty Straight Blade Flanged Receptacle
Type	2 Pole, 3 Wire, Grounding
Rating	15A, 250V
Certification	UL Listed, File E2186, Meets NEMA WD-6 requirements Listed to UL Standard 498, Certified to CSA, C22.2, No. 42
Terminal Screw Material	#8-32 Brass, Multiple Drive
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)
Top Material	Phenolic
Base Material	Phenolic
Power Contacts Material	.037" (.9) Phosphor Bronze
Mounting Screw Material	Brass-Nickel Plated
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).

Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only.
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 V2.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).



Hubbell Incorporated (Delaware)
 185 Plains Road
 Milford, CT 06460-2420
 Ph: (203) 882-4800
 Fax: (800) 255-1031

