




FAG

2212-K-TVH-C3

Self-aligning ball bearing

Self-aligning ball bearing 22..-K-TVH, tapered bore taper 1:12, plastic cage

Technical information



Your current product variant

Bore type	K	Tapered, taper 1:12
Sealing	Without	Not sealed
Cage	TVH	Solid cage made of glass-fiber reinforced polyamid PA66
Tolerance class	PN	Normal (PN)
Lubricant	Without	Bearing not greased
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN

Main Dimensions & Performance Data

d	60 mm	Bore diameter
D	110 mm	Outside diameter
B	28 mm	Width
C _r	48,000 N	Basic dynamic load rating, radial
C _{0r}	16,500 N	Basic static load rating, radial
C _{ur}	1,040 N	Fatigue load limit, radial
n _G	6,300 1/min	Limiting speed
n _{gr}	6,400 1/min	Reference speed
≈m	1.046 kg	Weight



Mounting dimensions

d _{a min}	69 mm	Minimum diameter shaft shoulder
d _{a max}	73 mm	Maximum diameter shaft shoulder
D _{a max}	101 mm	Maximum diameter of housing shoulder
d _{b min}	65 mm	Minimum cavity diameter of the sleeve
B _{a min}	9 mm	Minimum cavity width of the sleeve
r _{a max}	1.5 mm	Maximum fillet radius

Dimensions

r _{min}	1.5 mm	Minimum chamfer dimension
D ₁	98.17 mm	Shoulder diameter outer ring
d ₁	76.6 mm	Shoulder diameter inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Calculation factors

e	0.23	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2.68	Dynamic axial load factor
Y ₂	4.15	Dynamic axial load factor
Y ₀	2.81	Static axial load factor

Additional information

H312	Adapter sleeve
------	----------------



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment