



Fuse-link, LV, 250 A, AC 660 V, DC 460 V, BS88, 53 x 160 mm, gL/gG, BS

Catalog No. **TKM250**

Similar to illustration

### Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	250
Rated voltage			AC 660 V DC 460 V
Construction size			BS88
Size			53 x 160 mm
Utilization category			gL/gG
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			centre-bolted tags
Standards/Regulations			BS88-1 IEC 60269-1
Optional accessories			fuse-holder RS400

### Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	250
Rated voltage		V	660
Voltage type			AC/DC
Rated switching capacity		kA	80
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

### Additional product information (links)

Product datasheet (pdf)	<a href="http://www1.cooperbusmann.com/pdf/3e2cace6-400d-4026-af91-49c5a8d88159.pdf">http://www1.cooperbusmann.com/pdf/3e2cace6-400d-4026-af91-49c5a8d88159.pdf</a>
-------------------------	---