

Zack marker strip - ZB 5,LGS:(1-100/VERP) - 1051867

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Zack marker strip, Strip, white, labeled, Printed horizontally: Consecutive numbers, Mounting type: Snap into tall marker groove, for terminal block width: 5.2 mm, Lettering field: 10.5 x 5.15 mm

The illustration shows various versions of the article



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 255701
Weight per Piece (excluding packing)	0.01 g
Custom tariff number	39269097
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width (a)	5 mm
-----------	------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Printing direction	Printed horizontally
Printing	Consecutive numbers
Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10

Zack marker strip - ZB 5,LGS:(1-100/VERP) - 1051867

Technical data

General

Marking mounting type	Snap into tall marker groove
-----------------------	------------------------------

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410