

## Cable feed-through sleeve - HC-KDT 11-12 - 1644119


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable feed-through sleeves, for conductor diameters of 11-12 mm, starting at 10 mm, a cable binder can be used as strain relief



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 895976
Weight per Piece (excluding packing)	5.15 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Material	Thermoplastic rubber
Inflammability class according to UL 94	HB

### Classifications

#### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109

## Cable feed-through sleeve - HC-KDT 11-12 - 1644119

### Classifications

#### ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

#### UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

### Approvals

#### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

#### Approval details

EAC
-----

### Drawings

Dimensioned  
drawing

Dimensional  
drawing