



Relays, Contactors & Switches > Switches > Rocker Switches



Rocker Switch Type: **Power**

Rocker Switch Mounting Type: **Panel**

Indicator/Imprint Legend: **None**

Panel Cutout Size: **13 x 15.9 mm [.511 x .62 in]**

Switch Contact Plating Material: **Silver**

Features

Product Type Features

Product Type	Switch
Rocker Switch Type	Power
Lamp	Without
Rocker Switch LED	Without
Actuator Type	Top
Actuator Style	Paddle

Configuration Features

Indicator/Imprint Legend	None
Panel Cutout Size	13 x 15.9 mm[.511 x .62 in]
Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On On

Electrical Characteristics

Rocker Switch Voltage Rating	125 VAC, 250 VAC
------------------------------	------------------

Body Features

Body Color	Black
Actuator Color	Black

Contact Features

Switch Contact Plating Material	Silver
---------------------------------	--------



Rocker Switch Contact Current Rating	6 A
--------------------------------------	-----

Termination Features

Termination Type	Lead Wire - Hooking Type
------------------	--------------------------

Mechanical Attachment

Mounting Angle	Vertical
Rocker Switch Mounting Type	Panel

Housing Features

Process Sealed	No
----------------	----

Industry Standards

VDE Tested	No
------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 2-6437630-0
FTD0904=MINIATURE TOGGLE

TE Part # 5-6437630-0
AWTR1504 = POWER TOGGLE

TE Part # 6-6437630-1
FTN59G04=LOCKING TOGGLE

TE Part # 8-6437630-0
A4TK15W04

TE Part # 7-6437630-2
AWTN1504 = POWER TOGGLE

Customers Also Bought

TE Part #3-1415055-1
Force Guided Power Relay, 4 Poles

TE Part #1393260-7
SR6B4024 - V23050-A1024-A542

TE Part #166053-1
COSI PIN CONTACT HD20 DF; 24-20 AWG

TE Part #1-917511-3
DYNAMIC D-3 REC CONT. 2L AU 0.76 L/P

TE Part #1-406541-5
MJ,INV,1X1,0PNL G.,100"ST,SN

TE Part #104479-9
SHORT POINT CONT 15 DPLX STMPD LF

TE Part #178964-8
DYNAMIC D-3 W-T-W TAB HSG 20P

TE Part #1871731-1
DYNAMIC D1000 REC CONT 2L PRE TIN REEL

TE Part #170084-2
250 FASTON,REC.,18-14 AWG,TPPB



Documents

Product Drawings

FLD19BLACK04=LEVER ACTION SWITCH

English

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English

F_SERIES_SWITCHES_QUICK_REF_GUIDE_1-1773458-9

English