

Product data sheet

Specifications



Repacked, residual current circuit breaker (RCCB), Acti9 iID, 4P, 63A, A-SI type, 300mA, selective

A9R35463W



This repacked option saves 3.446 over the standard condition

Main

Range	Acti9
Product name	Acti9 iID
Product or component type	Residual current circuit breaker (RCCB)
Device short name	iID
Poles description	4P
Neutral position	Left
[In] rated current	63 A
Network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Selective
Earth-leakage protection class	Type A-SI (Super Immunised)

Complementary

Device location in system	Outgoer
Network frequency	50/60 Hz
[Ue] rated operational voltage	380...415 V AC 50/60 Hz
Residual current tripping technology	Voltage independent
Rated breaking and making capacity	Idm 1500 A Im 1500 A
Rated conditional short-circuit current	10 kA
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Contact position indicator	Yes
Control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	91 mm
Width	72 mm
Depth	73.5 mm
Product weight	0.37 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	White
Mechanical durability	20000 cycles
Electrical durability	AC-1: 15000 cycles
Locking options description	Padlocking device
Connections - terminals	Single terminal top or bottom 1...35 mm² rigid Single terminal top or bottom 1...25 mm² flexible Single terminal top or bottom 1...25 mm² flexible with ferrule
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom

Environment

Standards	EN/IEC 61008-1
Product certifications	EAC
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Electromagnetic compatibility	8/20 µs impulse withstand, 3000 A conforming to EN/IEC 61008-1
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.2 cm
Package 1 Width	7.5 cm
Package 1 Length	9.8 cm
Package 1 Weight	363.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	10.248 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

3 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

A7b24ae6-2312-4e67-b7c9-56fce3e8c723

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Offer Marketing Illustration

Product benefits / Features

Technical Benefits
Acti9 iID

