






THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		F	REVISED PER ECR-10-006099	09JUL10	HMR	PD

1. CONTINUOUS STRIP ON REELS.
2. WIRE RANGE: #12-#10 AWG,
INSULATION RANGE: .125-.220 DIA.



	TIN	H04 COPPER	62613-3
	TIN	TEMP 2 COLD ROLLED STEEL	62613-2
OBSOLETE	—	— ANNEALED STAINLESS STEEL	62613-1
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17NOV2004 MICHAEL S. FEHER	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK 30NOV2004 DONALD F. DECKER		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RING, ANTIROTATIONAL, 10 STUD SIZE —	
	0 PLC ± -			
	1 PLC ± -			
	2 PLC ± -		SIZE A2	
	3 PLC ± .010			
	4 PLC ± -			
MATERIAL SEE TABLE		FINISH SEE TABLE	CAGE CODE 00779	
			DRAWING NO C=62613	
			RESTRICTED TO —	
			SCALE 5:1	
			SHEET 1 OF 1	
			REV F	