



Product: [8770NH](#)

Electronic, 3C #18 Str TC, PO ins, OS, LSNH Jkt 300V

Product Description

Electronic, 3 Conductor AWG 18 Tinned Copper - Stranded, Polyolefin (PO, PE, PP) insulation, Foil(s) or Copper Tape(s) shielding, LSZH / FRNC jacket , 300V

Technical Specifications

Product Overview

Suitable Applications:	Audio, Control & Instrumentation cable; For data transmission applications
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	18 AWG	16x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PE - Polyethylene	0.018 in (0.46 mm)	0.082 in (2.1 mm)	Black, Red, Clear

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	20 AWG (7x28) TC

Outer Jacket

Material		Nom. Thickness	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)		0.84 mm (0.033 in)	6.25 mm (0.246 in)

Overall Cable Diameter (Nominal):	0.246 in.
-----------------------------------	-----------

Electrical Characteristics

Electricals					
Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
6.5 Ohm/1000ft	78.7 pF/m (24.0 pF/ft)	157.5 pF/m (48.01 pF/ft)	69 Ohm	66%	4.8 Amps per Conductor at 25°C
Voltage					
UL Voltage Rating	Voltage Rating				
300 V	300 V				

Mechanical Characteristics

Temperature		
UL Temperature	Operating	Installation
75°C	-20°C To +75°C	-15°C To +80°C
Bend Radius		
Stationary Min.	Installation Min.	

2.46 in (62.5 mm)	2.46 in
-------------------	---------

Max. Pull Tension:	100 lbs (45 kg)
Bulk Cable Weight:	37 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Non-Halogenated
CPR Compliance:	CPR Euroclass: Dca-s1,d1,a1
ISO/IEC Compliance:	IEC 61034-2 - Smoke Density Min Transmittance = 60%
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

History

Update and Revision:	Revision Number: 0.318 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
8770NH.00305	Chrome	Reel	305 m	8719605019240

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.