

HBA68MFZRE

✓ ACTIVE

CGS | CGS HB

TE Internal #: 1-1625960-1

68M ohm, Through-Hole High Value/High Voltage Resistor, Thick Film, .4 W, 1 %, ±100 ppm/°C, Radial-Leaded, Copper Termination, 8 x 2.6 mm, CGS HB

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistance Value: **68M Ω**

Resistor Type: **High Value/High Voltage Resistor**

Element Type: **Thick Film**

Power Rating: **.4 W**

Resistance Class: **1M Ω – 1G Ω**

Features

Product Type Features

Resistor Type	High Value/High Voltage Resistor
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	1000 V
Resistance Value	68M Ω
Power Rating	.4 W
Resistance Class	1M Ω – 1G Ω
Passive Component Tolerance	1 %

Body Features

Lead Type	Radial-Leaded
-----------	---------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	8 x 2.6 mm
------------------------------	------------



Usage Conditions

Operating Temperature Range	-55 – 125 °C
Temperature Coefficient	±100 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Tray
------------------	--------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (5% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

HBA68MFZRE

68M ohm, Through-Hole High Value/High Voltage Resistor, Thick Film, .4 W, 1 %, ±100 ppm/°C, Radial-Leaded, Copper Termination, 8 x 2.6 mm, CGS HB



TE Part # 1625960-1
HBA RE 100M 1% 100PPM

TE Part # 2-1625959-5
HB03RE 50M 1% 100PPM

TE Part # 1625958-4
HB01RE 100M 1% 100PPM

TE Part # 1625958-8
HB01RE 10M 1% 100PPM

TE Part # 1625959-3
HB03RE 100M 1% 100PPM

Also in the Series | CGS HB

Through-Hole Resistors(43)

Customers Also Bought

TE Part #3-1622796-3
YR1 0.1% 5K49

TE Part #1971567-2
MINIATURE HERMAPHRODITIC (4P)

TE Part #8-215570-0
MICRO-MATCH PBC.10P

TE Part #1-1623773-1
C10 1K0 5% (LOOSE)

TE Part #9-215079-0
MICRO-MATCH FOB.20P


TE Part #3-1879664-3
H8 2K49 0.1% 15PPM

TE Part #1393219-3
PE014005


TE Part #3-1879501-7
CRGH2512 5% 33R 2W

HBA68MFZRE

68M ohm, Through-Hole High Value/High Voltage Resistor, Thick Film, .4 W, 1 %, ±100 ppm/°C, Radial-Leaded, Copper Termination, 8 x 2.6 mm, CGS HB



TE Part #7-5530843-0
CONN SEC II 31 POS 100C/L



TE Part #7-1879664-9
H8 7K5 0.1% 15PPM

Documents

Product Drawings

HBA RE 68M 1% 100PPM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1625960-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1625960-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1625960-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

High Value/High Voltage Resistors - Type HB Series

English