

Backpack Mist Blower XGT®

PM001G

15 L, 14,0 m

Model PM001G is a cordless backpack mist blower powered by 40Vmax XGT® Li-Ion battery (two in parallel or one).

It provides added convenience in a wide range of applications due to many features and benefits such as: Very long max spray range, close to that of engine modes. 3 spraying speed modes for a wider range of applications. Solution supply valve interlocked with switch trigger to suppress dripping of solution.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Brushless Motor	✓
Container Capacity	15 L
No load speed	13800 - 16900 / 14700 - 20700 / 15800 - 25000 min ⁻¹
Max. Air Velocity	42,0 / 52,0 / 64,0 m/s
Air volume	9,0 / 11,0 / 14,3 m ³ / min
Maximum flow rate	858 m ³ / h
International Protection Class (IP)	IPX4
Vibration Level, No load	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), No load	1,5 m/s ²
Sound Power Level (L _{WA})	103,6 dB(A)
Sound Pressure Level (L _{pA})	86,6 dB(A)

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Brushless maintenance-free and long-life motor
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing