



Connectors > Connector Accessories > Connector Caps & Covers > Pin Connector: Strain Relief, Universal



Connector Cover Type: **Strain Relief Cover**
Primary Product Color: **Black**
Primary Product Material: **Glass-Filled Polyester**

[All Pin Connector: Strain Relief, Universal \(12\)](#)

Features

Product Type Features

Connector Cover Type	Strain Relief Cover
----------------------	---------------------

Body Features

Primary Product Color	Black
Primary Product Material	Glass-Filled Polyester

Dimensions

	1.14 in
--	---------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	CSA LR7189, UL E28476

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-111492-6
014 UNIV I/O 30DP NO EARS LTCH



TE Part # 1-111504-5
014 UNIV I/O 30DP NO EARS LTCH



TE Part # 1-111446-5
14 UNIV I/O, NO EARS,LEAD FREE

Customers Also Bought



TE Part #749087-2
50SR SCREWLOCK KIT,FEMALE



TE Part #1-2319747-6
TRI-STATE DIP 4P G RAISED T&R



TE Part #499252-2
020 STRAIN RELIEF A-L RCPT



TE Part #CAT-HST-RT375
RT-375 Heat Shrink Tubing





TE Part #810033-000
2019D0309-0



TE Part #66507-4
HD 20 DF PIN PLTD



TE Part #2302454-1
1-PORT MATENET FRAME,UTP, COD
A



TE Part #5-103956-1
10X2 MTE RCPT SR LATCH .100CL



TE Part #2-1393531-5
V23535A3280C 61=BKMOD422FEDERL

Documents

Product Drawings

014 UNIV I/O STRAIN RELIEF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_111547-2_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_111547-2_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_111547-2_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Ribbon Cable Interconnect Solutions

English

Product Specifications

Application Specification

English