




EMI & EMC Solutions > EMI Filters > Power Entry Modules > IEC Filtered Inlets, Corcom EJH Series



Filter Type: **Power Line**

Product Orientation: **Right Angle**

Leakage Current (Max) (120VAC, 60Hz): **2 μ A**

Leakage Current (Max) (250VAC, 50Hz): **5 μ A**

Current Rating: **15 A**

[All IEC Filtered Inlets, Corcom EJH Series \(19\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	2 μ A
Leakage Current (Max) (250VAC, 50Hz)	5 μ A
Current Rating	15 A
Operating Voltage	250 VAC

Body Features

Product Orientation	Right Angle
---------------------	-------------

Mechanical Attachment



Panel Mount Feature Type	Flange
--------------------------	--------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Corcom EJH



Power Entry Modules(19)


Customers Also Bought




TE Part #6609007-3
20EEJ1=F7892A S0




TE Part #41292
250 FASTON,TAB,BR




TE Part #60618-5
CMNL PIN AUBR L/P




TE Part #1-87309-4
MOD V RECP LP



TE Part #1609146-2
PA102 CONNECTOR PIN=F6999




TE Part #1-87456-2
16 MODIV HSG DR MRKD .100CL



TE Part #2-1761606-5
IDC LOW PRO HDR 14P VERT LA



TE Part #8-6609107-3
PS0SXSSXB=C1269



TE Part #62261-1
250 FASTON TAB BR



TE Part #6-87523-9
MOD IV RECP LP LF

Documents

Product Drawings
15EJH2=F8052

English

CAD Files
Customer View Model
ENG_CVM_1-6609008-4_C.3d_igs.zip

English

Customer View Model
ENG_CVM_1-6609008-4_C.3d_stp.zip

English

Customer View Model
ENG_CVM_1-6609008-4_C.2d_dxf.zip

English

3D PDF

English

Customer View Model
ENG_CVM_CVM_1-6609008-4_D.3d_igs.zip

English



Customer View Model

[ENG_CVM_CVM_1-6609008-4_D.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-6609008-4_D.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE_EEJ_SERIES](#)

English

Corcom Combined Selector Charts

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English