

This document was generated on 10/09/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 43045-0218

Status: **Active**

Micro-Fit 3.0™ Connectors **Overview:**

Micro-Fit 3.0™ Header, Surface Mount, Dual Row, Vertical, with Solder Tab, 2 Circuits, **Description:**

Tin (Sn) Plating, Glow Wire Compatible

Documents:

3D Model Test Summary TS-43045-001 (PDF) Drawing (PDF) RoHS Certificate of Compliance (PDF)

Product Specification PS-43045 (PDF) Product Literature (PDF)

Agency Certification

CSA LR19980 TUV R72081037 UL E29179

General

PCB Headers **Product Family** 43045

Series

Application Power, Wire-to-Board Comments

"High Temperature|Square Pin|Solder Type<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for


possible product options."

Micro-Fit 3.0™ Connectors Overview

Product Literature Order No 987650-5984 Micro-Fit 3.0™ **Product Name UPC** 800754370189

Physical

Breakaway No Circuits (Loaded) 2 Circuits (maximum) 2 Color - Resin Black Durability (mating cycles max) 30 Flammability 94V-0 **Glow-Wire Compliant** Yes Mated Height 17.27mm Material - Metal **Brass** Material - Plating Mating Tin Material - Plating Termination Tin



EU RoHS ELV and RoHS Compliant **REACH SVHC Contains SVHC: No Low-Halogen Status** Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com For a multiple part number RoHS Certificate of Compliance, click here

Please visit the Contact Us section for any non-product compliance questions.

Search Parts in this Series

43045Series

Mates With

43025 Micro-Fit 3.0™ Receptacle Housing

Material - Resin High Temperature Thermoplastic

Net Weight0.730/gNumber of Rows2OrientationVerticalPCB LocatorYesPCB RetentionYesPCB Thickness - Recommended1.60mm

Packaging Type Embossed Tape on Reel

Pitch - Mating Interface 3.00mm
Plating min - Mating 0.254µm
Polarized to PCB Yes
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) N/A

Temperature Range - Operating -40°C to +105°C Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 5A Voltage - Maximum 600V

Solder Process Data

Duration at Max. Process Temperature (seconds) 30

Lead-free Process Capability Reflow Capable (SMT only)

Max. Cycles at Max. Process Temperature 3
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Product Specification PS-43045, RPS-43045-003, RPS-43045-004

Sales Drawing SD-43045-007 Test Summary TS-43045-001

This document was generated on 10/09/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION