

Eaton 134845

Catalog Number: 134845

Eaton SPX Variable frequency drive, 400 V AC, 3-phase, 132 kW, IP21, Radio interference suppression filter, Brake chopper, OLED display, FR9



General specifications

Product Name	Catalog Number
Eaton SPX variable frequency drive	134845
EAN	Product Length/Depth
4015081316908	1150 mm
Product Height	Product Width
362 mm	480 mm
Product Weight	Certifications
146 kg	IEC/EN 61800-3
	RoHS, ISO 9001
	CE
	DNV
	IEC/EN61800-3
	Specification for general requirements:
	IEC/EN 61800-2
	UL Category Control No.: NMMS,
	NMMS2, NMMS7. NMMS8
	IEC/EN61800-5
	UL 508C
	Certified by UL for use in Canada
	UL
	CUL
	UL File No.: E134360
	CSA-C22.2 No. 14
	Safety: EN 61800-5-1: 2003
	UL report applies to both US and
	Canada
	RCM
	CSA Class No.: 3211-06

General

Degree of protection

IP21

NEMA Other

Electromagnetic compatibility

1st and 2nd environments (according to EN 61800-3)

Fitted with:

Internal DC link

Radio interference suppression filter

IGBT inverter

Brake chopper

DC link choke

OLED display

Frame size

FR9

Mounting position

Vertical

Product Category

Variable frequency drives

Protection

Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)

Radio interference class

C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary.

Suitable for

Branch circuits, (UL/CSA)

Climatic environmental conditions

Altitude

Max. 1000 m

Max. 3000 m

Above 1000 m with 1 % performance reduction per 100 m

Ambient operating temperature - min

-10 °C

Ambient operating temperature - max

40 °C

Ambient operating temperature at 150% overload - min

-10 °C

Ambient operating temperature at 150% overload - max

50 °C

Ambient storage temperature - min

-40 °C

Climatic proofing

< 95 % relative humidity, no condensation, no corrosion, no dripping water

Main circuit

Mains voltage - min

380 V

Mains voltage - max

500 V

Operating mode

Sensorless vector control (SLV)

U/f control

Optional: Vector control with feedback (CLV)

Output frequency - min

0 Hz

Output frequency - max

320 Hz

Output voltage (U₂)

480 V AC, 3-phase

500 V AC, 3-phase

400 V AC, 3-phase

Rated control supply voltage

10 V DC (Us, max. 10 mA)

Rated frequency - min

45 Hz

Rated frequency - max

66 Hz

Rated operational current (Ie) at 110% overload

300 A

Rated operational current (Ie) at 150% overload

245 A

Rated operational power at 380/400 V, 50 Hz

132 kW

Rated operational power at 380/400 V, 50 Hz, 110% overload

160 kW

Rated operational voltage

400 V AC, 3-phase

480 V AC, 3-phase

500 V AC, 3-phase

Resolution

0.01 Hz (Frequency resolution, setpoint value)

Supply frequency

50/60 Hz

Switching frequency

3.6 kHz, 1 - 10 kHz adjustable, fPWM, Power section, Main circuit

System configuration type

AC supply systems with earthed center point

Voltage rating - max

480 VAC

Communication

Communication interface

PROFIBUS-DP

BACnet/IP, optional

LonWorks, optional

DeviceNet, optional

CANopen®, optional

Motor rating

Assigned motor current IM at 400 V, 50 Hz, 110% overload

279 A

Assigned motor current IM at 400 V, 50 Hz, 150% overload

231 A

Assigned motor current IM at 440 - 480 V, 60 Hz, 150% overload

240 A

Assigned motor current IM at 440/480 V, 60 Hz, 110% overload

302 A

Assigned motor power at 460/480 V, 60 Hz

200 HP

Assigned motor power at 460/480 V, 60 Hz, 110% overload

250 HP

Control circuit

Number of inputs (analog)

2 (parameterizable, 0 - 10 V DC, 0/4 - 20 mA)

Number of inputs (digital)

6 (parameterizable, max. 30 V DC)

Number of outputs (analog)

1

Number of outputs (digital)

1 (parameterizable, 48 V DC/50 mA)

Number of relay outputs

2 (parameterizable, N/O, 8 A (24 V DC) / 8 A (250 V AC) / 0,4 A (125 V DC))

Rated control voltage (Uc)

24 V DC (external, max. 250 mA)

Design verification

Equipment heat dissipation, current-dependent Pvid

3300 W

Rated operational current for specified heat dissipation (In)

245 A

10.2.2 Corrosion resistance

Modbus-TCP, optional
BACnet MS/TP, optional
EtherCAT, optional
Ethernet IP, optional
Modbus-RTU, optional
PROFINET, optional

Connection to SmartWire-DT

No

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise

calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Resources

Application notes

[Electromagnetic compatibility \(EMC\)](#)

[Connecting drives to generator supplies](#)

[SPI - Variable frequency drives with a common DC bus](#)

Catalogs

[Product Range Catalog Drives Engineering](#)

Declarations of conformity

[DA-DC-00004868.pdf](#)

[DA-DC-00004869.pdf](#)

Drawings

[eaton-frequency-inverter-dimensions-008.eps](#)

Installation instructions

[IL04020008Z](#)

Multimedia

[Eaton variable frequency drives - Demand more innovation](#)

[Eaton variable frequency drives - Demand more expertise](#)

[Eaton variable frequency drives - Demand more than good enough](#)

[How does a VFD work to save energy and money?](#)

Product notifications

[eaton-drives-ecodesign-directive-mz040046en-en.pdf](#)