



Brand of NTN corporation

## Technical data



### 6011C3

Single row deep groove ball bearings



Deep groove ball bearing, radial contact, pressed steel cage, open

#### VISUAL (S)



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

# 6011C3

Single row deep groove ball bearings

## PRODUCT DEFINITION

|                                   |          |
|-----------------------------------|----------|
| Brand                             | SNR      |
| d - Internal diameter             | 55 mm    |
| D - External diameter             | 90 mm    |
| B - Bearing/Inner ring width      | 18 mm    |
| d1 - External diameter inner ring | 63,7 mm  |
| D1 - Inner diameter outer ring    | 82,1 mm  |
| rs - Min fillet radius            | 1,1 mm   |
| Radial clearance class            | C3       |
| Mass                              | 0,382 kg |

## PRODUCT PERFORMANCE

|                                  |             |
|----------------------------------|-------------|
| C - Dynamic load                 | 29800000 mN |
| C0 - Static load                 | 21300000 mN |
| Cu - Fatigue limit load          | 970000 mN   |
| f0 - Coefficient                 | 15.4        |
| N ref - Reference thermal speed  | 49800 °/s   |
| N lim - Mechanical Limit Speed   | 72000 °/s   |
| Tmin - Min operating temperature | 233,15 °K   |
| Tmax - Max operating temperature | 393,15 °K   |

## BEARING FREQUENCIES

|                                                          |          |
|----------------------------------------------------------|----------|
| BPFO - Over rolling frequency on outer ring (60 rpm)     | 5.575 Hz |
| BPFI - Over rolling frequency on inner (60 rpm)          | 7.425 Hz |
| BSF - Over rolling frequency on rolling element (60 rpm) | 6.884 Hz |
| BRF - Rotational frequency - rolling element (60 rpm)    | 3.442 Hz |



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

## BEARING FREQUENCIES

FTF - Rotational frequency - cage (60 rpm)

0.429 Hz

## ABUTMENT

da min - Min shoulder diameter IR

61,5 mm

Da max - Max shoulder diameter OR

83,5 mm

ra max - Max shaft &amp; housing fillet radius

1 mm

## INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

| $\frac{f_0 F_a}{C_0}$ | e    | Fa / Fr ≤ e |   | Fa / Fr > e |      |
|-----------------------|------|-------------|---|-------------|------|
|                       |      | X           | Y | X           | Y    |
| 0.172                 | 0.19 | 1           | 0 | 0.56        | 2.3  |
| 0.345                 | 0.22 |             |   |             | 1.99 |
| 0.689                 | 0.26 |             |   |             | 1.71 |
| 1.03                  | 0.28 |             |   |             | 1.55 |
| 1.38                  | 0.3  |             |   |             | 1.45 |
| 2.07                  | 0.34 |             |   |             | 1.31 |
| 3.45                  | 0.38 |             |   |             | 1.15 |
| 5.17                  | 0.42 |             |   |             | 1.04 |
| 6.89                  | 0.44 |             |   |             | 1    |

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

| $X_0$ | $Y_0$ |
|-------|-------|
| 0.6   | 0.5   |

For single or DT bearing arrangement:

If  $P_0 < F_r$ , then use  $P_0 = F_r$ 

NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15