



Connectors > Automotive Connectors > Automotive Housings > Circular DIN Housings



Number of Positions: 4

Connector & Housing Type: **Housing for Male Terminals**

Mating Pin Diameter: 1.5 mm [.059 in]

Connector System: **Wire-to-Wire**

Sealable: **Yes**

[All Circular DIN Housings \(59\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Circular
Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Blank Cavity Position	5, 6, 7
Number of Positions	4

Electrical Characteristics

Operating Voltage	48 VDC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V



Body Features

Cable Exit Angle	180°
Primary Product Color	Black
Connector & Keying Code	A

Contact Features

Contact Size	1.5mm
Contact Type	Pin
Mating Pin Diameter	1.5 mm[.059 in]

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF
------------------	--------

Dimensions

Product Width	44 mm[1.732 in]
Product Length	39.2 mm[1.546 in]
Connector Height	39.26 mm[1.546 in]

Usage Conditions

Operating Temperature (Max)	120 °C[248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

IP Rating	IP67, IP6K9K
UL Flammability Rating	UL 94HB

Packaging Features

Packaging Quantity	450
Packaging Method	Box & Carton



Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C4962-CH8172
Circular DIN Housings




TE Part # CAT-C4962-B128
Circular DIN Backshells




TE Part # CAT-R7602-T273
ROUND CONNECTOR SYSTEM, PIN AND SOCKET

Customers Also Bought







TE Part #CAT-R7602-T273
ROUND CONNECTOR SYSTEM, PIN AND SOCKET




TE Part #828922-1
2,5MM CAVITY PLUG FOR 5,4MM DI




TE Part #60390-1
SPADE CRIMP 20-16 AWG BR




TE Part #61627-2
.140 DIA PIN 20-14 PTPPHBZ




TE Part #2-521104-2
ULTRA-FAST 187 ASY REC 22-18 TPBR




TE Part #967650-1
1.5MM BU-STE KPL 7P



TE Part #2-521361-2
ULTRAFAST 187 ASSY TAB 22-18 AWG TPBR



TE Part #40723
RING 138(3.50 MM) TERMINAL18-14 AWG TPBR



TE Part #2-22287-6
SPRING,EXTENSION

Documents

Product Drawings
1,5MM PIN HSG 5-7 POS ASSY
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1718230-4_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1718230-4_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1718230-4_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English