

## PS316-T12-J300



- Design to EN 50041
- cable entry 1 x M20 x 1,5
- length adjustable in 2 mm steps
- Lever angle adjustable in 15° steps
- thermoplastic enclosure with foldable latching cover
- Simple and quick to adjust the control elements by 45°.
- Quick connection technology as connection terminals rotated by 45°

### Data

#### Ordering data

Product type description	PS316-T12-J300
Article number (order number)	103015164
EAN (European Article Number)	4030661502618

#### Certifications

Certificates	cULus CCC EAC
--------------	---------------------

#### General data

Product name	PS316 with rod lever J300
Standards	IEC 60947-5-1
Housing construction form	Norm construction design
Enclosure material	Plastic, glass-fibre-reinforced
Material of the contacts, electrical	Silver
Gross weight	158 g

#### General data - Features

Number of auxiliary contacts	1
------------------------------	---

Number of safety contacts 2

### Safety appraisal

Standards ISO 13849-1

Mission Time 20 Year(s)

### Safety appraisal - Safety outputs

B10d Normally-closed contact (NC) 20,000,000 Operations

### Mechanical data

Actuating element Rod lever J300

Mechanical life, minimum 10,000,000 Operations

Positive break force, minimum 50 N

Actuating speed, minimum 60 mm/min

Actuating speed, maximum 1 m/s

### Mechanical data - Connection technique

Terminal Connector Screw connection

Cable section, minimum 0.34 mm<sup>2</sup>

Cable section, maximum 1.5 mm<sup>2</sup>

### Mechanical data - Dimensions

Height of sensor 192 mm

Length of sensor 37 mm

Width of sensor 41 mm

### Ambient conditions

Protection class IP66

IP67

Ambient temperature, minimum -30 °C

Ambient temperature, maximum +80 °C

### Ambient conditions - Insulation value

Rated impulse withstand voltage 4 kV

### Electrical data

Thermal test current 5 A

Required rated short-circuit current to EN 60947-5-1 400 A

Utilisation category AC-15 240 VAC

Utilisation category AC-15 3 A

Utilisation category DC-13 24 VDC

Utilisation category DC-13	3 A
Switching element	1 NO contact, 2 NC contacts
Switching principle	Creep circuit element
Switching frequency	5,000 /h

## Ordering code

Product type description:

PS(2)-(3)-(4)-(5)-(6)-(7)-(8)-(9)-(10)-(11)-  
(12)

(2)

**315** Metal enclosure

**316** Thermoplastic enclosure

(3)

**without** L-hole (standard)

**L** elongated hole

(4)

**Z11** Snap action 1 NO contact / 1 NC contact

**Z02** Snap action 2 NC contacts

**Z12** Snap action 1 NO contact / 2 NC contact

**Z11R** Snap action 1 NO contact / 1 NC contact with latching

**Z02R** Snap action 2 NC contacts with latching

**T11** Slow action 1 NO contact / 1 NC contact

**T02** Slow action 2 NC contacts

**T20** Slow action 2 NO contact

**T12** Slow action 1 NO contact / 2 NC contact

**T21** Slow action 2 NO contact / 1 NC contact

**T03** Slow action 3 NC contacts

**T11UE** Slow action 1 NO contact / 1 NC contact with overlapping contacts

**T02H** Slow action 2 NC contacts with staggered contacts

(5)

**without** Contacts silver plated (Standard)

**A1** Gold contacts 0,3 µm

**A2** Gold contacts 1,0 µm

**A3** Gold contacts 3,0 µm

(6)

**without** without indication light

**G** integrated status display

(7)

**without** Cable entry M20

**ST** Connector plug M12 - plastic - bottom

**STM** Connector plug M12, metal

(8)

**S200** plunger S200 Ø 6 mm

**S300** Plunger - plastic - tappet width Ø 9 mm

**R300** Roller plunger - plastic roller - width 4.6 mm

**R302** Roller plunger - brass roller - width 4.6 mm

**K360** Angle roller lever with plastic roller Ø 20 mm - left-bent

**K370** Angle roller lever with plastic roller Ø 20 mm - right-bent

**H300** Roller lever - plastic roller Ø 25 mm

**H301** Roller lever - stainless steel roller Ø 25 mm

**H302** Roller lever - brass roller Ø 25 mm

**H310** Roller lever - plastic roller Ø 20 mm

**H311** Roller lever - stainless steel roller Ø 20 mm

**H312** Roller lever - brass roller Ø 20mm

**H326** Roller lever - rubber roller Ø 20mm

**N300** Roller lever - plastic roller Ø 25 mm

**N301** Roller lever - stainless steel roller Ø 20 mm

**N306** Roller lever - rubber roller Ø 20mm

**N360** Roller lever - plastic roller Ø 20 mm - width 9.8 mm - long

**N370** Roller lever - plastic roller Ø 20 mm - width 9.8 mm - very long

**J300** Rod lever - plastic - 200mm -Ø 6mm

**F230** Spring rod - plastic

**F231** Spring rod - stainless steel

**A200** Special actuating bolt - plastic - valve control

(9)

**without** no intent rotation (Standard)

**U1** intent rotation 45°

**U2** intent rotation 90°

**U3** intent rotation 135°

**U4** intent rotation 180°

**U5** intent rotation 225°

**U6** intent rotation 275°

**U7** intent rotation 315°

(10)

**without** no lever rotation (Standard)

<b>X1</b>	lever rotation 15°
<b>X2</b>	lever rotation 30°
<b>X3</b>	lever rotation 45°
<b>X4</b>	lever rotation 60°
<b>X5</b>	lever rotation 75°
<b>X6</b>	lever rotation 90°
<b>X7</b>	lever rotation 105°
<b>X8</b>	lever rotation 120°
<b>X9</b>	lever rotation 135°
<b>X10</b>	lever rotation 150°
<b>X11</b>	lever rotation 165°
<b>X12</b>	lever rotation 180°
<b>X13</b>	lever rotation 195°
<b>X14</b>	lever rotation 210°
<b>X15</b>	lever rotation 225°
<b>X16</b>	lever rotation 240°
<b>X17</b>	lever rotation 255°
<b>X18</b>	lever rotation 270°
<b>X19</b>	lever rotation 285°
<b>X20</b>	lever rotation 300°
<b>X21</b>	lever rotation 315°
<b>X22</b>	lever rotation 330°
<b>X23</b>	lever rotation 345°

(11)

**without** Roller outside (Standard)

**I** Roller inside

(12)

**without** -30...+80°C (Standard)

**T** -40...+80°C

## Documents

### Operating instructions and Declaration of conformity

(444,8 kB, 19.11.2019)

### Operating instructions (supplementary sheet/quick guide)

(408,0 kB, 10.05.2019, Revision A)

## UL Certificate

(211,5 kB, 01.08.2019)

## CCC certification

(6,9 MB, 21.08.2019)

## EAC certification

## SISTEMA-VDMA library

(134,9 kB, 19.06.2019)

## Pictures

### Product picture (catalogue individual photo)



ID: kps3jf02

| 98,9 kB | .jpg | 27.093 x 83.058 mm - 320 x 981 Pixel - 300 dpi

| 55,2 kB | .png | 74.083 x 227.189 mm - 210 x 644 Pixel - 72 dpi

| 932,1 kB | .jpg | 352.778 x 1081.969 mm - 1000 x 3067 Pixel - 72 dpi

### Product picture (catalogue individual photo)




ID: kps3jf03

| 40,9 kB | .png | 74.083 x 206.022 mm - 210 x 584 Pixel - 72 dpi

| 61,3 kB | .jpg | 27.093 x 75.353 mm - 320 x 890 Pixel - 300 dpi

| 606,7 kB | .jpg | 352.778 x 981.781 mm - 1000 x 2783 Pixel - 72 dpi

### Dimensional drawing basic component




ID: kps3xg01

| 5,0 kB | .png | 74.083 x 70.203 mm - 210 x 199 Pixel  
- 72 dpi

| 140,3 kB | .jpg | 352.778 x 333.728 mm - 1000 x 946  
Pixel - 72 dpi

| 35,0 kB | .jpg | 112.889 x 106.892 mm - 320 x 303  
Pixel - 72 dpi

### Switch travel diagram




ID: kps11s61

| 23,4 kB | .jpg | 112.889 x 55.739 mm - 320 x 158  
Pixel - 72 dpi

| 2,3 kB | .png | 74.083 x 36.689 mm - 210 x 104 Pixel  
- 72 dpi


### Diagram



ID: kps2xk02

| 24,0 kB | .jpg | 112.889 x 47.272 mm - 320 x 134  
Pixel - 72 dpi

### Dimensional drawing actuator



ID: kps3xb07

| 4,3 kB | .png | 74.083 x 81.844 mm - 210 x 232 Pixel  
- 72 dpi

| 148,3 kB | .jpg | 352.778 x 409.928 mm - 1000 x  
1162 Pixel - 72 dpi

K.A. Schmersal GmbH & Co. KG, Möddinghofe 3, D-42279 Wuppertal

The details and data referred to have been carefully checked. Images may diverge from original. Further technical data can be found in the manual. Technical amendments and errors possible.

Generated on 23.06.2020 16:42:20