
| REV | DESCRIPTION | DRAWN | DATE |
|-----|-------------|-------|------|
| | | | |
| | | | |



| 4 | PRESS FIT FERRULE | 1 | BRASS | NICKEL | UNLESS OTHERWISE SPECIFIED 1.REMOVE ALL BURRS. | * MAJOR DIMENSION UNLESS OTHERWISE | APPROVED | ▲ Siretta |
|----|-------------------|------|----------|--------|--|------------------------------------|---------------------|-----------------------------------|
| 3 | DIELECTRIC | 2 | TEFLON | NONE | 2.BREAK ALL CONNERS & EDGES CO.15 MAX. | NOTED TOLERANCES 0.5-6=±0.2 | CHECKED | Enabling Industrial IoT |
| 2 | PIN | 1 | BRASS | GOLD | - 3.CHAMFER 1ST & LAST THREADS 45°. 4.DIAMETERS ON COMMON | $6-30=\pm0.4$ $30-120=\pm0.6$ | DDAWA | SMA JACK TO FME PLUG |
| 1 | BODY | 1 | BRASS | NICKEL | CENTERS. TO BE CONCENTRIC WITHIN 0.1 T.I.R. 5.ALL DIMENSIONS ARE | 120-315=±1.0 ANGLES=±1° | andrew | DRAWING NO. ADAPT/FMEM/SMAF REV A |
| NO | Description | Q'ty | Material | Finish | 5.ÄLL DIMENSIONS ARE AFTER PLATING. | SCALE 5/2 UNIT MM | DRAWN DATE 03/06/20 | FILE NO. |