
# TLS205B0 DEMO Board User Guide





### Board Overview and Quick Start





#### **Quick Start**


- Select the desired Output Voltage V<sub>OUT</sub>:
  - close **ONE** of the jumpers JMP 1-5 according to page 2. If JMP5 is used (= user-specific) a user defined value for R5 must be soldered accordingly. If  $V_{OUT} > 16V$  is chosen the output capacitor must be replaced with a capacitor having a higher voltage rating (16V is assembled). Leave the other jumpers open!
- > Select Bypass Capacitance:
  - the jumper settings of SV1 allow to use pre-assembled bypass capacitor values C<sub>BYP</sub> of either 10nF or 1nF. Leaving SV1 open corresponds to "no bypass capacitor used".
- Connect GND to Ground
- Connect V<sub>IN</sub> to the Voltage Supply
  - Absolute Maximum Rating  $V_{IN}$ : -20V to 20V
- Connect V<sub>out</sub> to the load
  - Absolute Maximum Rating V<sub>OUT</sub>: -20V to 20V
- > Set EN to high level or connect to V<sub>IN</sub> to start the voltage regulator
  - Absolute Maximum Rating EN: -20V to 20V
  - Jumper JMP6 can be used to tie  $V_{EN}$  to  $V_{IN}$

#### **Note:** Do NOT exceed the Absolute Maximum Ratings!



#### **Board Schematics**








#### **Board TOP Layer**










#### **Board BOTTOM Layer**







## Part of your life. Part of tomorrow.

