

## Han TC400\_CT\_SMC\_M\_CRT\_120mm²\_Ag



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 6576
Specification	Han TC400_CT_SMC_M_CRT_120mm²_Ag
HARTING eCatalogue	<a href="https://harting.com/09110006576">https://harting.com/09110006576</a>

### Identification

Category	Contacts
Series	TC 400
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

#### Details

The vibration and shock resistance can only be met if the cables are fixed at an appropriate distance. Instructions for the spacing of strain relief can be found in the document in eCatalogue under the section Instructions.

### Technical characteristics

Conductor cross-section	120 mm²
Rated current	≤400 A
Contact resistance	≤0.3 mΩ
Stripping length	22.5 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Vibration resistance	Category 2 acc. to IEC 61373
Shock resistance	Category 2 acc. to IEC 61373

### Material properties

Material (contacts)	Copper alloy
---------------------	--------------



**Pushing Performance**  
Since 1945

## Material properties

Surface (contacts)	Silver plated
--------------------	---------------

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	1
Net weight	68.08 g
Country of origin	Germany
European customs tariff number	85359000
GTIN	5713141118248
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522