

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 19.11.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** Perchlorure de fer liquide, 2 x 2,5 litres Réf : AR412
Perchloride liquid iron, 2 x 2.5L Ref : AR412
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
commercial and / or industrial use
- **Application of the substance / the preparation :** Reagent
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
CIF
240 rue Hélène Boucher
78530 BUC
Tél : 01.39.66.96.83 – Fax 01.33.66.97.78
E-mail : cif@cif.fr – Web : www.cif.fr
- **1.4 Emergency telephone number:**
France (ORFILA 24h/24) - Tel : +33 (0)1 45 42 59 59
Ireland - Tel : 00 353 1 8092568 - 00 353 1 8379964 (24h/24)
UK : +44 (0)-870-190-6777 (CARECHEM24)

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008 :**



GHS05

- Met. Corr.1 H290 May be corrosive to metals.
- Skin Corr. 1A H314 Causes severe skin burns and eye damage.
- Eye Dam. 1 H318 Causes serious eye damage.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**



GHS05

- **Signal word** Danger
- **Hazard-determining components of labelling:**
iron trichloride
- **Hazard statements**
H290 May be corrosive to metals.
H314 Causes severe skin burns and eye damage.
- **Precautionary statements**
P260 Do not breathe dust/fume/gas/mist/vapours/spray.
P280 Wear protective gloves/protective clothing/eye protection/face protection.
P234 Keep only in original container.
P264 Wash hands thoroughly after handling.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 19.11.2015

Trade name: Perchlorure de fer liquide, 2 x 2,5 litres Réf : AR4122
Perchloride liquid iron, 2 x 2.5L Ref : AR4122

(Contd. of page 1)

- P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.*
- P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.*
- P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.*
- P301+P330+P331 IF SWALLOWED: rinse mouth. Do NOT induce vomiting.*
- P406 Store in corrosive resistant container with a resistant inner liner.*
- P501 Dispose of contents/container in accordance with local/regional/national/international regulations.*

- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Chemical characterisation: Mixtures**
- **Description:** Mixture: consisting of the following components.

· **Dangerous components:**

CAS: 7705-08-0	iron trichloride	25-50%
EINECS: 231-729-4	Met. Corr.1, H290; Eye Dam. 1, H318; Aquatic Chronic 2, H411;	
RTECS: LJ 9100000	Acute Tox. 4, H302; Skin Irrit. 2, H315	

- **Additional information:** For the wording of the listed risk phrases, refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **General information:**
Immediately remove any clothing soiled by the product.
Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.
- **After excessive inhalation:**
In case of unconsciousness place patient in a stable laying down side position for transportation.
- **After skin contact:** *Immediately wash with water and soap and rinse thoroughly.*
- **After eye contact:** *Rinse opened eye for several minutes under running water. Then consult a doctor.*
- **After swallowing:**
Call for a doctor immediately.
Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed :**
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed :**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Suitable extinguishing agents:**
CO2, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture :**
Formation of toxic gases is possible during heating or in case of fire.

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 19.11.2015

Trade name: Perchlorure de fer liquide, 2 x 2,5 litres Réf : AR4122
Perchloride liquid iron, 2 x 2.5L Ref : AR4122

(Contd. of page 2)

- **5.3 Advice for firefighters**
- **Protective equipment:** Mouth respiratory protective device.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures :**
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:**
Dilute with plenty of water.
Do not allow the product to enter sewers/ surface water or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Use neutralising agent.
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **6.4 Reference to other sections :**
See Section 7 for information on safe handling.
See Section 8 for information on personal protective equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling :**
Ensure good ventilation/exhaustion at the workplace.
Prevent formation of aerosols.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store only in the original receptacle.
- **Information about storage in one common storage facility:**
Store away from water.
Store away from flammable substances.
Store away from foodstuffs.
Store away from metals.
Do not store together with oxidising and acidic materials.
- **Further information about storage conditions:** Keep container tightly sealed.
- **7.3 Specific end use(s) :** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see section 7.
- **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

7705-08-0 iron trichloride (25-50%)

WEL (Great Britain)	Short-term value: 2 mg/m ³ Long-term value: 1 mg/m ³ as Fe
---------------------	--

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 19.11.2015

Trade name: Perchlorure de fer liquide, 2 x 2,5 litres Réf : AR4122
Perchloride liquid iron, 2 x 2.5L Ref : AR4122

(Contd. of page 3)

MAK (Switzerland)	Long-term value: 1e mg/m ³ als Fe berechnet
-------------------	---

· **Additional information:**

The most current valid lists have been used as a basis for the production of this document.

· **8.2 Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Keep away from food, beverages and petfood.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Avoid contact with the eyes and skin.

· **Respiratory protection:**



In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

· **Gloves material :**

The selection of suitable gloves does not depend only on the material, but also on further marks of quality which may vary from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked before use.

· **Eye protection:**



Tightly sealed goggles

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form: Liquid

Colour: Brown

· **Odour:** Pungent

· **Odour threshold:** Not determined.

· **pH-value at 20 °C:** < 1

· **Change in condition**

Melting point/Melting range: Undetermined.

Boiling point/Boiling range: 110 °C

(Contd. on page 5)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 19.11.2015

Trade name: *Perchlorure de fer liquide, 2 x 2,5 litres Réf : AR4122*
Perchloride liquid iron, 2 x 2.5L Ref : AR4122

(Contd. of page 4)

· Flash point:	Not applicable.
· Flammability (solid, gaseous):	Not applicable.
· Ignition temperature:	Not applicable.
· Decomposition temperature:	160 °C
· Self-igniting:	Product is not self igniting.
· Danger of explosion:	Product does not present an explosion hazard.
· Explosion limits:	
Lower:	Not determined.
Upper:	Not determined.
· Vapour pressure at 20 °C:	17 mbar
· Density at 20 °C:	1,43 g/cm ³ (40%)
· Relative density :	Not determined.
· Vapour density :	Not determined.
· Evaporation rate :	Not determined.
· Solubility in / Miscibility with water:	Fully miscible.
· Segregation coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· 9.2 Other information :	No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions :**
Reacts with water and acids.
Reacts with strong acids and oxidising agents.
Reacts with various metals.
- **10.4 Conditions to avoid :** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:**
Chlorine
Hydrogen
Hydrogen chloride (HCl)

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

(Contd. on page 6)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 19.11.2015

Trade name: Perchlorure de fer liquide, 2 x 2,5 litres Réf : AR4122
Perchloride liquid iron, 2 x 2.5L Ref : AR4122

(Contd. of page 5)

· **LD/LC50 values relevant for classification:**

7705-08-0 iron trichloride

Oral	LD50	1872 mg/kg (rat)
------	------	------------------

· **Primary irritant effect:**

· **On the skin:**

Causes severe skin burns and eye damage.

· **On the eyes:**

Causes serious eye damage.

· **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.

· **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**

· **Germ cell mutagenicity** Based on available data, the classification criteria are not met.

· **Carcinogenicity** Based on available data, the classification criteria are not met.

· **Reproductive toxicity** Based on available data, the classification criteria are not met.

· **STOT-single exposure** Based on available data, the classification criteria are not met.

· **STOT-repeated exposure** Based on available data, the classification criteria are not met.

· **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

· **12.1 Toxicity**

· **Aquatic toxicity:** No further relevant information available.

· **12.2 Persistence and degradability :** No further relevant information available.

· **12.3 Bioaccumulative potential :** No further relevant information available.

· **12.4 Mobility in soil :** No further relevant information available.

· **Additional ecological information:**

· **General notes:**

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water.

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

Must not reach sewage water or drainage ditch undiluted or unneutralised.

Throwing away bigger amounts into drains or aquatic environment may lead to decreased pH-values. A low pH-value harms aquatic organisms. In the diluted product use, the pH-value is considerably increased, so that after the use of the product the aqueous waste, emptied into drains, is only slightly polluting for water.

· **12.5 Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

· **12.6 Other adverse effects :** No further relevant information available.

SECTION 13: Disposal considerations

· **13.1 Waste treatment methods**

· **Recommendation :**



Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

· **Uncleaned packaging:**

· **Recommendation:** Disposal must be made according to official regulations.

(Contd. on page 7)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 19.11.2015

Trade name: *Perchlorure de fer liquide, 2 x 2,5 litres Réf : AR4122*
Perchloride liquid iron, 2 x 2.5L Ref : AR4122

(Contd. of page 6)

· **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

SECTION 14: Transport information

· **14.1 UN-Number**

· **ADR, IMDG, IATA** UN2582

· **14.2 UN proper shipping name**

· **ADR** UN2582 FERRIC CHLORIDE SOLUTION
 · **IMDG** FERRIC CHLORIDE SOLUTION
 · **IATA** Ferric chloride, solution

· **14.3 Transport hazard class(es)**

· **ADR**



· **Class** 8 (C1) Corrosive substances.
 · **Label** 8

· **IMDG, IATA**



· **Class** 8 Corrosive substances.
 · **Label** 8

· **14.4 Packing group**

· **ADR, IMDG, IATA** III

· **14.5 Environmental hazards:**

· **Marine pollutant:** No

· **14.6 Special precautions for user**

· **Danger code (Kemler):** Warning: Corrosive substances.
 80
 · **EMS Number:** F-A,S-B
 · **Segregation groups** Acids
 · **Stowage Category** A

· **14.7 Transport in bulk according to Annex II of Marpol and the IBC Code**

Not applicable.

· **Transport/Additional information:**

· **ADR**

· **Limited quantities (LQ)** 5L
 · **Excepted quantities (EQ)** Code: E1
 Maximum net quantity per inner packaging: 30 ml
 Maximum net quantity per outer packaging: 1000 ml

· **Transport category** 3
 · **Tunnel restriction code** E

(Contd. on page 8)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.11.2015

Version number 1

Revision: 19.11.2015

Trade name: Perchlorure de fer liquide, 2 x 2,5 litres Réf : AR4122
Perchloride liquid iron, 2 x 2.5L Ref : AR4122

(Contd. of page 7)

- | | |
|--|--|
| <ul style="list-style-type: none"> · IMDG · Limited quantities (LQ) · Excepted quantities (EQ) | 5L
Code: E1
Maximum net quantity per inner packaging: 30 ml
Maximum net quantity per outer packaging: 1000 ml |
| <ul style="list-style-type: none"> · UN "Model Regulation": | UN 2582 FERRIC CHLORIDE SOLUTION, 8, III |

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
No further relevant information available.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
H290 May be corrosive to metals.
H302 Harmful if swallowed.
H315 Causes skin irritation.
H318 Causes serious eye damage.
H411 Toxic to aquatic life with long lasting effects.
- **Abbreviations and acronyms:**
ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
Met. Corr. 1: Corrosive to metals, Hazard Category 1
Acute Tox. 4: Acute toxicity, Hazard Category 4
Skin Corr. 1A: Skin corrosion/irritation, Hazard Category 1A
Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2
Eye Dam. 1: Serious eye damage/eye irritation, Hazard Category 1
Aquatic Chronic 2: Hazardous to the aquatic environment - Chronic Hazard, Category 2