

SHOWA

660

CHEMICAL PROTECTION


Durable, oil-resistant, triple-dipped PVC glove

Strong, yet extremely soft and flexible. The 660 features a soft comfortable cotton lining and the rough textured coating ensures grip and increases the glove's abrasion resistance and durability. The gloves are also oil and chemical resistant. Available in 3 different lengths.

Features

- ▲ Seals and protects the hand against chemicals while remaining flexible
- ▲ Impermeable for working in damp or greasy environments, enabling you to grip objects securely
- ▲ Excellent abrasion resistance (EN388 Level 4)
- ▲ Surface provides tactile feel and better grip
- ▲ Greater hygiene
- ▲ Designed for easy movement and continuous wear
- ▲ No irritation by seams in contact with the skin
- ▲ Forearm well protected

Certifications



Suitable industries & applications

Industries

- ▲ Food Production
- ▲ Manufacturing
- ▲ Chemicals
- ▲ Oil and Gas
- ▲ Maritime
- ▲ Utilities

Applications

- ▲ Component and Product Assembly
- ▲ Chemical Handling and Containment
- ▲ Commercial Cleaning
- ▲ Fossil Fuel Extraction and Refining
- ▲ Metal Forging and Processing
- ▲ Commercial Vehicles



Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Durable, oil-resistant, triple-dipped PVC glove

Product information

Materials	Liner:	Cotton
	Coating:	PVC
Colour	Blue	
Cuff Style	Gauntlet	

Ordering information

M	SHO660B2	Items per Pack 10 x Pairs
L	SHO660B3	
XL	SHO660B4	Items per Case 60 x Pairs
XXL	SHO660B5	

Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.