

# Eaton 135676

Catalog Number: 135676

Eaton Moeller® series E58 Diffuse reflective sensor, Sn=150mm, 4L, 10-30VDC, dark, NPN, PNP, M30, metal, line 2m

### General specifications



Product Name	Catalog Number
Eaton Moeller® series E58 Diffuse reflective sensor	135676
	EAN
	4015081324699
Product Length/Depth	Product Height
228.6 mm	44.45 mm
Product Width	Product Weight
152.4 mm	0.45 kg

### Certifications

CE  
CSA File No.: UL report applies to both  
US and Canada  
CSA-C22.2 No. 14  
Certified by UL for use in Canada  
UL  
IEC/EN 60947-5-2  
UL Category Control No.: NRKH, NRKH7

UL 508  
UL File No.: E166051

## Product specifications

### Type

Optical sensors

### Electric connection type

Cable

### Fitted with:

Background suppression (Perfect Prox)

### Enclosure material

Metal

### Enclosure type

Cylinder, screw-thread

### Operating mode

Switching principle: Dark switching

### Explosion safety category for dust

None

### Explosion safety category for gas

None

### Functions

Reflected-light beam

Protection against polarity reversal

Short-circuit protection

Protection against wire breakage

### Voltage type

DC

### Wire size

22

### Connection type

4-wire

2 m connection cable

### Cable sheath material

Polyvinyl chloride (PVC)

### Light type

Other

### Degree of protection

NEMA 6

IP68

### Interface type

## Resources

### Catalogs

Product Range Catalog Sensors – products, basic information, applications

### Declarations of conformity

DA-DC-00004657.pdf

DA-DC-00004652.pdf

### Drawings

eaton-proximity-switches-e58-diffuse-reflective-sensor-dimensions-002.eps

eaton-proximity-switches-e58-diffuse-reflective-sensor-3d-drawing.eps

### Installation instructions

IL05305003Z

Other

#### LED indicator

Status indication of Switching state: Red LED

#### Switch function type

Other

#### Load current

Max. 100 mA (I<sub>e</sub>)

#### Laser protection class

None

#### Operation agent-safety class

Safety class 2

#### Shock resistance

100 g, Mechanical, Shock duration 3 ms

#### Optical surface material

Glass

#### Output current (mA) - max

100 mA

#### Output current at protected output - max

0 mA

#### Rated control supply voltage (U<sub>s</sub>) at AC, 50 Hz - max

0 V

#### Rated control supply voltage (U<sub>s</sub>) at AC, 50 Hz - min

0 V

#### Rated control supply voltage (U<sub>s</sub>) at AC, 60 Hz - max

0 V

#### Rated control supply voltage (U<sub>s</sub>) at AC, 60 Hz - min

0 V

#### Rated control supply voltage (U<sub>s</sub>) at DC - max

30 V

#### Rated control supply voltage (U<sub>s</sub>) at DC - min

10 V

#### Rated switching distance (S<sub>n</sub>)

150 mm

#### Reflector distance - min

0 mm

#### Sensor height

0 mm

Sensor length

111 mm

Switching distance - max

165 mm

Switching voltage of OSSD at state high

30 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

312 Hz

Sensing mode

Dark switching

Switching output type

NPN

Sensor material

Stainless steel

Triangulation

Background fade-out

Wavelength of the sensor

660 nm

Width sensor

0 mm

Product category

E58 Harsh Duty Series

Response time

1.6 ms

Adjustment range - max

150 mm

Adjustment range - min

0 mm

Ambient operating temperature - max

55 °C

Ambient operating temperature - min

-40 °C

Diameter sensor

30 mm

Light dot size

0 mm²

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

2

Operating distance - max

0 mm

Operating distance - min

0 mm

Adjustment type

Other



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia