16-bit buffer/line driver; 30  $\Omega$  series termination resistors; 5 V tolerant input/output; 3-state Rev. 7 — 11 February 2019

Product data sheet

## 1. General description

The 74LVC162244A; 74LVCH162244A are 16-bit non-inverting buffer/line drivers with 3-state bus compatible outputs. The device can be used as four 4-bit buffers, two 8-bit buffers or one 16-bit buffer. It features four output enable inputs, (1OE to 4OE) each controlling four of the 3-state outputs. A HIGH on nOE causes the outputs to assume a high-impedance OFF-state. The device is designed with 30 Ω series termination resistors in both HIGH and LOW output stages to reduce line noise.

Inputs can be driven from either 3.3 V or 5 V devices. When disabled, up to 5.5 V can be applied to the outputs. These features allow the use of these devices in mixed 3.3 V and 5 V applications.

The 74LVCH162244A bus hold on data inputs eliminates the need for external pull-up resistors to hold unused inputs.

# 2. Features and benefits

- 5 V tolerant inputs/outputs for interfacing with 5 V logic
- Wide supply voltage range from 1.2 V to 3.6 V
- CMOS low power consumption
- Multibyte flow-through standard pin-out architecture
- · Low inductance multiple power and ground pins for minimum noise and ground bounce
- Direct interface with TTL levels
- High-impedance when V<sub>CC</sub> = 0 V
- All data inputs have bus hold. (74LVCH162244A only)
- Complies with JEDEC standard:
  - JESD8-7A (1.65 V to 1.95 V)
  - JESD8-5A (2.3 V to 2.7 V)
  - JESD8-C/JESD36 (2.7 V to 3.6 V)
- ESD protection
  - HBM JESD22-A114F exceeds 2000 V
  - MM JESD22-A115-B exceeds 200 V
  - CDM ANSI/ESDA/Jedec JS-002 exceeds 1000 V
- Specified from -40 °C to +85 °C and -40 °C to +125 °C

# nexperia


# 3. Ordering information


### Table 1. Ordering information

Type number	Temperature range	Package			
		Name	Description	Version	
74LVC162244ADL	-40 °C to +125 °C	SSOP48	plastic shrink small outline package; 48 leads;	SOT370-1	
74LVCH162244ADL			body width 7.5 mm		
74LVC162244ADGG	-40 °C to +125 °C	TSSOP48	plastic thin shrink small outline package;	SOT362-1	
74LVCH162244ADGG			48 leads; body width 6.1 mm		
74LVC162244ADGV	-40 °C to +125 °C	TSSOP48 [1]	plastic thin shrink small outline package;	SOT480-1	
74LVCH162244ADGV	1		48 leads; body width 4.4 mm; lead pitch 0.4 mm		


[1] Also known as TVSOP48.

# 4. Functional diagram





# 5. Pinning information



### 5.1. Pinning

### 5.2. Pin description

### Table 2. Pin description

Symbol	Pin	Description
10E, 20E, 30E, 40E	1, 48, 25, 24	output enable input (active LOW)
1Y0 to 1Y3	2, 3, 5, 6	data output
2Y0 to 2Y3	8, 9, 11, 12	data output
3Y0 to 3Y3	13, 14, 16, 17	data output
4Y0 to 4Y3	19, 20, 22, 23	data output
GND	4, 10, 15, 21, 28, 34, 39, 45	ground (0 V)
V <sub>CC</sub>	7, 18, 31, 42	supply voltage
1A0 to 1A3	47, 46, 44, 43	data input
2A0 to 2A3	41, 40, 38, 37	data input
3A0 to 3A3	36, 35, 33, 32	data input
4A0 to 4A3	30, 29, 27, 26	data input

# 6. Functional description

### Table 3. Function table

H = HIGH voltage level; L = LOW voltage level; X = don't care; Z = high-impedance OFF-state.

	Input	Output
nOE	nAn	nYn
L	L	L
L	Н	Н
Н	X	Z

# 7. Limiting values

### Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V <sub>CC</sub>	supply voltage			-0.5	+6.5	V
I <sub>IK</sub>	input clamping current	V <sub>I</sub> < 0 V		-50	-	mA
VI	input voltage		[1]	-0.5	+6.5	V
I <sub>OK</sub>	output clamping current	$V_{\rm O}$ > $V_{\rm CC}$ or $V_{\rm O}$ < 0 V		-	±50	mA
Vo	output voltage	output HIGH or LOW	[2]	-0.5	V <sub>CC</sub> + 0.5	V
		output 3-state	[2]	-0.5	+6.5	V
I <sub>O</sub>	output current	$V_{O} = 0 V$ to $V_{CC}$		-	±50	mA
I <sub>CC</sub>	supply current			-	100	mA
I <sub>GND</sub>	ground current			-100	-	mA
T <sub>stg</sub>	storage temperature			-65	+150	°C
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = -40 °C to +125 °C;	[3]	-	500	mW

The minimum input voltage ratings may be exceeded if the input current ratings are observed. [1]

[2] [3] The output voltage ratings may be exceeded if the output current ratings are observed.

Above 60 °C the value of Ptot derates linearly with 5.5 mW/K.

# 8. Recommended operating conditions

### Table 5. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
V <sub>CC</sub>	supply voltage		1.65	-	3.6	V
		functional	1.2	-	3.6	V
VI	input voltage		0	-	5.5	V
Vo	output voltage	output HIGH or LOW	0	-	V <sub>CC</sub>	V
		output 3-state	0	-	5.5	V
T <sub>amb</sub>	ambient temperature	in free air	-40	-	+125	°C
Δt/ΔV	input transition rise and fall rate	V <sub>CC</sub> = 1.2 V to 2.7 V	0	-	20	ns/V
		V <sub>CC</sub> = 2.7 V to 3.6 V	0	-	10	ns/V

# 9. Static characteristics

### Table 6. Static characteristics

At recommended operating conditions. Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	-40	°C to +8	5 °C	-40 °C to +125 °C		Unit
			Min	Typ [1]	Max	Min	Max	
VIH	HIGH-level	V <sub>CC</sub> = 1.2 V	1.08	-	-	1.08	-	V
	input voltage	V <sub>CC</sub> = 1.65 V to 1.95 V	0.65V <sub>CC</sub>	-	-	0.65V <sub>CC</sub>	-	V
		V <sub>CC</sub> = 2.3 V to 2.7 V	1.7	-	-	1.7	-	V
		V <sub>CC</sub> = 2.7 V to 3.6 V	2.0	-	-	2.0	-	V
VIL	LOW-level	V <sub>CC</sub> = 1.2 V	-	-	0.12	-	0.12	V
	input voltage	V <sub>CC</sub> = 1.65 V to 1.95 V	-	-	0.35V <sub>CC</sub>	-	0.35V <sub>CC</sub>	V
		V <sub>CC</sub> = 2.3 V to 2.7 V	-	-	0.7	-	0.7	V
		V <sub>CC</sub> = 2.7 V to 3.6 V	-	-	0.8	-	0.8	V
V <sub>OH</sub>	HIGH-level	$V_{I} = V_{IH} \text{ or } V_{IL}$						
	output voltage	$I_{O}$ = -100 µA; V <sub>CC</sub> = 1.65 V to 3.6 V	V <sub>CC</sub> - 0.2	-	-	V <sub>CC</sub> - 0.3	-	V
		I <sub>O</sub> = -2 mA; V <sub>CC</sub> = 1.65 V	1.2	-	-	1.05	-	V
		$I_{\rm O}$ = -4 mA; $V_{\rm CC}$ = 2.3 V	1.7	-	-	1.55	-	V
		$I_{\rm O}$ = -6 mA; $V_{\rm CC}$ = 2.7 V	2.2	-	-	2.05	-	V
		I <sub>O</sub> = -12 mA; V <sub>CC</sub> = 3.0 V	2.2	-	-	2.0	-	V
V <sub>OL</sub>	LOW-level	$V_{I} = V_{IH} \text{ or } V_{IL}$						
	output voltage	I <sub>O</sub> = 100 μA; V <sub>CC</sub> = 1.65 V to 3.6 V	-	-	0.2	-	0.3	V
		I <sub>O</sub> = 2 mA; V <sub>CC</sub> = 1.65 V	-	-	0.45	-	0.65	V
		I <sub>O</sub> = 4 mA; V <sub>CC</sub> = 2.3 V	-	-	0.6	-	0.8	V
		I <sub>O</sub> = 6 mA; V <sub>CC</sub> = 2.7 V	-	-	0.4	-	0.6	V
		I <sub>O</sub> = 12 mA; V <sub>CC</sub> = 3.0 V	-	-	0.55	-	0.8	V
I	input leakage current	V <sub>CC</sub> = 3.6 V; V <sub>I</sub> = 5.5 V or GND	-	±0.1	±5	-	±20	μA
I <sub>OZ</sub>	OFF-state output current	$V_{I} = V_{IH} \text{ or } V_{IL}; V_{CC} = 3.6 \text{ V};$ $V_{O} = 5.5 \text{ V or GND}$	[2] -	±0.1	±5	-	±20	μA
I <sub>OFF</sub>	power-off leakage current	$V_{CC}$ = 0 V; V <sub>I</sub> or V <sub>O</sub> = 5.5 V	-	±0.1	±10	-	±20	μA
I <sub>CC</sub>	supply current	$V_{CC}$ = 3.6 V; $V_{I}$ = $V_{CC}$ or GND; $I_{O}$ = 0 A	-	0.1	20	-	80	μA
ΔI <sub>CC</sub>	additional supply current	per input pin; $V_{CC} = 2.7 V \text{ to } 3.6 V;$ $V_I = V_{CC} - 0.6 V; I_O = 0 A$	-	5	500	-	5000	μA
CI	input capacitance	$V_{CC}$ = 0 V to 3.6 V; V <sub>I</sub> = GND to V <sub>CC</sub>	-	5.0	-	-	-	pF
I <sub>BHL</sub>	bus hold LOW	V <sub>CC</sub> = 1.65; V <sub>I</sub> = 0.58 V [3]	[4] 10	-	-	10	-	μA
	current	V <sub>CC</sub> = 2.3; V <sub>I</sub> = 0.7 V	30	-	-	25	-	μA
		V <sub>CC</sub> = 3.0; V <sub>I</sub> = 0.8 V	75	-	-	60	_	μA

74LVC\_LVCH162244A

### 16-bit buffer/line driver; 30 $\Omega$ series termination resistors; 5 V tolerant input/output; 3-state

Symbol	Parameter	Conditions	-40	-40 °C to +85 °C			-40 °C to +125 °C		
			Min	Typ [1]	Max	Min	Max		
I <sub>BHH</sub>	bus hold HIGH	V <sub>CC</sub> = 1.65; V <sub>I</sub> = 1.07 V [3] [4]	-10	-	-	-10	-	μA	
	current	V <sub>CC</sub> = 2.3; V <sub>I</sub> = 1.7 V	-30	-	-	-25	-	μA	
		V <sub>CC</sub> = 3.0; V <sub>I</sub> = 2.0 V	-75	-	-	-60	-	μA	
I <sub>BHLO</sub>	bus hold LOW	V <sub>CC</sub> = 1.95 V [3] [5]	200	-	-	200	-	μA	
	overdrive current	V <sub>CC</sub> = 2.7 V	300	-	-	300	-	μA	
	current	V <sub>CC</sub> = 3.6 V	500	-	-	500	-	μA	
I <sub>BHHO</sub>	bus hold HIGH	V <sub>CC</sub> = 1.95 V [3] [5]	-200	-	-	-200	-	μA	
	overdrive current	V <sub>CC</sub> = 2.7 V	-300	-	-	-300	-	μA	
	Current	V <sub>CC</sub> = 3.6 V	-500	-	-	-500	-	μA	

[1] All typical values are measured at V<sub>CC</sub> = 3.3 V and T<sub>amb</sub> = 25 °C.

[2] The bus hold circuit is switched off when  $V_I > V_{CC}$  allowing 5.5 V on the input terminal.

[3] Valid for data inputs only. Control inputs do not have a bus hold circuit.

[4] The specified sustaining current at the data input holds the input below the specified  $V_I$  level.

[5] The specified overdrive current at the data input forces the data input to the opposite logic input state.

# **10.** Dynamic characteristics

### Table 7. Dynamic characteristics

Voltages are referenced to GND (ground = 0 V). For test circuit see Fig. 7.

Symbol Parameter		meter Conditions		-40 °C to +85 °C			-40 °C to +125 °C		
			Min	Тур [1]	Max	Min	Max	-	
t <sub>pd</sub>	propagation	nAn to nYn; see Fig. 5 [2]							
	delay	V <sub>CC</sub> = 1.2 V	-	11.0	-	-	-	ns	
		V <sub>CC</sub> = 1.65 V to 1.95 V	1.5	6.0	15.0	1.5	17.2	ns	
		V <sub>CC</sub> = 2.3 V to 2.7 V	1.0	3.2	7.4	1.0	8.2	ns	
		V <sub>CC</sub> = 2.7 V	1.0	3.3	6.7	1.0	8.5	ns	
		V <sub>CC</sub> = 3.0 V to 3.6 V	1.0	2.7	5.8	1.0	7.5	ns	
t <sub>en</sub>	enable time	nOE to nYn; see Fig. 6 [2]							
		V <sub>CC</sub> = 1.2 V	-	15.0	-	-	-	ns	
		V <sub>CC</sub> = 1.65 V to 1.95 V	1.7	6.8	15.3	1.7	17.7	ns	
		V <sub>CC</sub> = 2.3 V to 2.7 V	1.5	3.8	8.0	1.5	8.9	ns	
		V <sub>CC</sub> = 2.7 V	1.5	4.2	7.6	1.5	9.5	ns	
		V <sub>CC</sub> = 3.0 V to 3.6 V	1.0	3.1	6.0	1.0	7.5	ns	
t <sub>dis</sub>	disable time	nOE to nYn; see Fig. 6 [2]							
		V <sub>CC</sub> = 1.2 V	-	10.0	-	-	-	ns	
		V <sub>CC</sub> = 1.65 V to 1.95 V	2.2	3.9	8.2	2.2	9.5	ns	
		$V_{CC}$ = 2.3 V to 2.7 V	0.5	2.1	4.4	0.5	5.0	ns	
		V <sub>CC</sub> = 2.7 V	1.5	3.1	4.7	1.5	6.0	ns	
		V <sub>CC</sub> = 3.0 V to 3.6 V	1.5	2.8	4.5	1.5	6.0	ns	

### 16-bit buffer/line driver; 30 $\Omega$ series termination resistors; 5 V tolerant input/output; 3-state

Symbol Parameter		Conditions		-40 °C to +85 °C			-40 °C to +125 °C	
			Min	Typ [1]	Max	Min	Max	
C <sub>PD</sub>	power	per input; $V_I = GND$ to $V_{CC}$ [3]						
	dissipation capacitance	V <sub>CC</sub> = 1.65 V to 1.95 V	-	4.8	-	-	-	pF
	capacitance	$V_{CC}$ = 2.3 V to 2.7 V	-	8.3	-	-	-	pF
		V <sub>CC</sub> = 3.0 V to 3.6 V	-	11.4	-	-	-	pF

Typical values are measured at  $T_{amb}$  = 25 °C and  $V_{CC}$  = 1.2 V, 1.8 V, 2.5 V, 2.7 V and 3.3 V respectively. [1]

[2]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ . ten is the same as tPZL and tPZH.  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ .

 $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu$ W).  $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma (C_L \times V_{CC}^2 \times f_0)$  where: [3]

 $f_i$  = input frequency in MHz;  $f_o$  = output frequency in MHz


CL = output load capacitance in pF

V<sub>CC</sub> = supply voltage in Volts

N = number of inputs switching

 $\Sigma(C_L \times V_{CC}^2 \times f_0)$  = sum of the outputs.


### 10.1. Waveforms and test circuit



Measurement points are given in Table 8.

V<sub>OL</sub> and V<sub>OH</sub> are typical output voltage levels that occur with the output load.

#### The input (nAn) to output (nYn) propagation delays Fig. 5.





#### Fig. 6. 3-state enable and disable times

74LVC\_LVCH162244A

### 16-bit buffer/line driver; 30 $\Omega$ series termination resistors; 5 V tolerant input/output; 3-state

Table 8. Measurement	t points		Output		
Supply voltage	Input	Input			
V <sub>cc</sub>	V <sub>M</sub>	VI	V <sub>M</sub>	V <sub>X</sub>	V <sub>Y</sub>
1.2 V	$0.5 \times V_{CC}$	V <sub>CC</sub>	$0.5 \times V_{CC}$	V <sub>OL</sub> + 0.15 V	V <sub>OH</sub> - 0.15 V
1.65 V to 1.95 V	$0.5 \times V_{CC}$	V <sub>CC</sub>	$0.5 \times V_{CC}$	V <sub>OL</sub> + 0.15 V	V <sub>OH</sub> - 0.15 V
2.3 V to 2.7 V	$0.5 \times V_{CC}$	V <sub>CC</sub>	$0.5 \times V_{CC}$	V <sub>OL</sub> + 0.15 V	V <sub>OH</sub> - 0.15 V
2.7 V	1.5 V	2.7 V	1.5 V	V <sub>OL</sub> + 0.3 V	V <sub>OH</sub> - 0.3 V
3.0 V to 3.6 V	1.5 V	2.7 V	1.5 V	V <sub>OL</sub> + 0.3 V	V <sub>OH</sub> - 0.3 V





Test data is given in Table 9.

Definitions for test circuit:

R<sub>L</sub> = Load resistance.

 $C_L$  = Load capacitance including jig and probe capacitance.

 $R_T$  = Termination resistance should be equal to output impedance  $Z_0$  of the pulse generator.


 $V_{EXT}$  = External voltage for measuring switching times.

### Fig. 7. Test circuit for measuring switching times

### Table 9. Test data

Supply voltage	Input		Load	Load		V <sub>EXT</sub>		
	VI	t <sub>r</sub> , t <sub>f</sub>	CL	RL	t <sub>PLH</sub> , t <sub>PHL</sub>	t <sub>PLZ</sub> , t <sub>PZL</sub>	t <sub>PHZ</sub> , t <sub>PZH</sub>	
1.2 V	V <sub>CC</sub>	≤ 2 ns	30 pF	1 kΩ	open	$2 \times V_{CC}$	GND	
1.65 V to 1.95 V	V <sub>CC</sub>	≤ 2 ns	30 pF	1 kΩ	open	$2 \times V_{CC}$	GND	
2.3 V to 2.7 V	V <sub>CC</sub>	≤ 2 ns	30 pF	500 Ω	open	$2 \times V_{CC}$	GND	
2.7 V	2.7 V	≤ 2.5 ns	50 pF	500 Ω	open	$2 \times V_{CC}$	GND	
3.0 V to 3.6 V	2.7 V	≤ 2.5 ns	50 pF	500 Ω	open	$2 \times V_{CC}$	GND	

# **11. Package outline**



### Fig. 8. Package outline SOT370-1 (SSOP48)

### 16-bit buffer/line driver; 30 $\Omega$ series termination resistors; 5 V tolerant input/output; 3-state





Fig. 9. Package outline SOT362-1 (TSSOP48)

### 16-bit buffer/line driver; 30 $\Omega$ series termination resistors; 5 V tolerant input/output; 3-state



# 12. Abbreviations

Acronym	Description
CDM	Charged Device Model
CMOS	Complementary Metal-Oxide Semiconductor
DUT	Device Under Test
ESD	ElectroStatic Discharge
НВМ	Human Body Model
MM	Machine Model
TTL	Transistor-Transistor Logic

# 13. Revision history

## Table 11. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes	
74LVC_LVCH162244A v.7	20190211	Product data sheet	-	74LVC_LVCH162244A v.6	
Modifications:	<ul> <li>The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia.</li> <li>Legal texts have been adapted to the new company name where appropriate.</li> <li>Type numbers 74LVC162244ADGV and 74LVCH162244ADGV (SOT480-1) added.</li> <li>Fig. 1: Logic symbol updated</li> <li>Package outline drawing <u>SOT362-1</u> (TSSOP48) updated.</li> </ul>				
74LVC_LVCH162244A v.6	20111216	Product data sheet	-	74LVC_LVCH162244A v.5	
Modifications:	<ul> <li>Maximum propagation delay value for V<sub>CC</sub> = 1.65 V to 1.95 V at +125 °C changed from 15.7 ns to 17.2 ns</li> <li>Maximum enable time value for V<sub>CC</sub> = 1.65 V to 1.95 V at +125 °C changed from 16.1 ns to 17.7 ns</li> <li>Maximum disable time value for V<sub>CC</sub> = 1.65 V to 1.95 V at +125 °C changed from 8.7 ns to 9.5 ns</li> </ul>				
74LVC_LVCH162244A v.5	20111108	Product data sheet	-	74LVC_LVCH162244A v.4	
Modifications:	<ul> <li>The format of this document has been redesigned to comply with the new identity guidelines of NXP Semiconductors.</li> <li>Legal texts have been adapted to the new company name where appropriate.</li> <li><u>Table 5</u>, <u>Table 6</u>, <u>Table 7</u> and <u>Table 9</u>: values added for lower voltage ranges.</li> </ul>				
74LVC_LVCH162244A v.4	20031212	Product specification	-	74LVC_H162244A v.3	
74LVC_H162244A v.3	19980217	Product specification	-	74LVC162244A_ LVCH162244A v.3	
74LVC162244A_ LVCH162244A v.3	19980217	Product specification	-	74LVC162244A v.2	
		Product specification			

# 14. Legal information

### Data sheet status

Document status [1][2]	Product status [3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

 Please consult the most recently issued document before initiating or completing a design.

- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <u>https://www.nexperia.com</u>.

#### **Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <u>http://www.nexperia.com/profile/terms</u>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### **Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

© Nexperia B.V. 2019. All rights reserved

# Contents

1. General description	1
2. Features and benefits	1
3. Ordering information	2
4. Functional diagram	2
5. Pinning information	3
5.1. Pinning	3
5.2. Pin description	3
6. Functional description	4
7. Limiting values	4
8. Recommended operating conditions	4
9. Static characteristics	5
10. Dynamic characteristics	6
10.1. Waveforms and test circuit	7
11. Package outline	9
12. Abbreviations	12
13. Revision history	12
14. Legal information	13

### © Nexperia B.V. 2019. All rights reserved

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com Date of release: 11 February 2019

74LVC\_LVCH162244A