

## Features

- Bushing with Threaded Blind Hole and Polished Zinc-Plated Steel
- Natural Rubber (NR), black color.
- 40, 55, 70 Shore A  $\pm 5$  (medium hardness for effective vibration damping).
- Damp vibrations, shocks, and noise from moving bodies or unbalanced vibrating masses.
- Prevents malfunctioning and extends machine lifespan.
- Reduces health risks caused by vibration exposure.
- Minimizes noise pollution.
- Ideal for equipment and machinery where vibration isolation is critical.
- Common in industrial, mechanical, and automation systems.

## RS PRO RS PRO Rubber Buffer Bushing with Threaded Blind Hole and Base Plate in Polished Zinc-Plated Steel, Vibration-Damper Body in Natural Rubber NR, Black Colour, Hardness 40, 55, 70 Shore A $\pm 5$



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### *RS PRO Rubber Buffers Bushing with Threaded Blind Hole and Polished Zinc-Plated Steel*

*The RS PRO range of rubber buffers is designed to absorb vibrations, shocks, and noise in machinery and equipment. These buffers feature a natural rubber (NR) body with a hardness of 40, 55, 70 Shore A  $\pm$ 5, combined with Base Plate in Polished Zinc-Plated Steel.*

*What are they used for?*

- To isolate vibrations and reduce noise generated by moving parts or unbalanced rotating masses.*
- To protect machinery and surrounding structures from damage caused by shocks and vibrations.*
- To extend equipment lifespan and improve operational stability.*

*Applications*

*Ideal for:*

- Industrial machinery*
- Compressors, pumps, and generators*
- HVAC systems*
- Automation and assembly lines*

*What are they used with?*

*Commonly paired with:*

- Motors and engines to reduce vibration transmission.*
- Machine frames and bases for stability*
- Sensitive equipment to prevent operational disturbances.*

## General Specifications

<b>Material – Metal Parts</b>	Polished Zinc-Plated Steel
<b>Material – Buffer Body</b>	Natural Rubber (NR), black color
<b>Hardness</b>	40, 55, 75 Shore A $\pm$ 5
<b>Mounting Type</b>	Bushing with Threaded Blind Hole
<b>Noise Reduction</b>	Yes
<b>Shock Absorption</b>	Yes
<b>Applications</b>	Industrial machinery, compressors, pumps, HVAC systems

## Similar Products

Stock No.	Diameter (mm)	Length (mm)	Thread Size	Hardness
0714907	20	17	M5	55
0714908	20	17	M6	55
0714909	25	17	M6	55
0714910	25	20	M6	55
0714911	32	22	M8	55
0714912	32	26	M8	55
0714913	38	32	M8	55
0714914	38	32	M10	55
0714915	38	35	M8	55
0714916	38	35	M10	55
0714918	43	50	M10	55
0714919	50	20	M10	55
0714920	50	43	M10	55
0714921	60	40	M10	55
0714922	20	17	M5	40
0714924	20	17	M6	40
0714925	25	17	M6	40
0714926	25	20	M6	40
0714927	32	22	M8	40
0714928	32	26	M8	40
0715164	38	32	M8	40
0715165	38	32	M10	40
0715166	38	35	M8	40
0715167	38	35	M10	40
0715168	43	50	M10	40
0715169	50	20	M10	40
0715170	50	43	M10	40
0715171	60	40	M10	40

Stock No.	Diameter (mm)	Length (mm)	Thread Size	Hardness
0715172	20	17	M5	70
0715173	20	17	M6	70
0715174	25	17	M6	70
0715175	25	20	M6	70
0715176	32	22	M8	70
0715177	32	26	M8	70
0715179	38	32	M8	70
0715180	38	32	M10	70
0715181	38	35	M8	70
0715182	38	35	M10	70
0715183	43	50	M10	70
0715185	50	20	M10	70
0715186	50	43	M10	70
0713763	60	40	M10	70



