



Figure similar

SIPLUS ET 200SP IM155-6PN ST / BA based on 6ES7155-6AA02-0BN0 with conformal coating, -40...+70 °C, PROFINET interface module IM 155-6 PN ST, max. 32 I/O modules, and 16 ET 200AL modules, multi hot swap, optional PN strain relief, bundle consists of: interface module (6AG1155-6AU02-7BN0), server module (6AG1193-6PA00-7AA0), BusAdapter BA 2xRJ45 (6AG1193-6AR00-7AA0)

| General information   |   |
|---|---|
| Product type designation  | IM 155-6 PN ST incl. BA 2x RJ45 and server module   |
| Firmware version  |   |
| <ul style="list-style-type: none"> <li>FW update possible</li> </ul>  | Yes   |
| Vendor identification (VendorID)  | 002AH   |
| Device identifier (DeviceID)  | 0313H   |
| Manufacturer ID according to ODVA (VendorID)  | 04E3H   |
| Device ID according to ODVA (Product code)  | 0FA2H   |
| based on  | <a href="#">6ES7155-6AA02-0BN0</a>  |
| Product function  |   |
| <ul style="list-style-type: none"> <li>I&amp;M data</li> <li>Module swapping during operation (hot swapping)</li> <li>Isochronous mode</li> <li>IRT</li> <li>Local coupling, IO data                             <ul style="list-style-type: none"> <li>Number of coupling modules</li> </ul> </li> </ul> | Yes; I&M0 to I&M4<br>Yes; Multi-hot swapping<br>No<br>Yes<br>6; 1x output + max. 5x input |
| Engineering with  |   |
| <ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated from version</li> </ul>  | see entry ID: 109746275   |
| Configuration control   |   |
| via dataset   | Yes   |
| Supply voltage  |   |
| Rated value (DC)  | 24 V  |
| permissible range, lower limit (DC)   | 19.2 V  |
| permissible range, upper limit (DC)   | 28.8 V  |
| Reverse polarity protection   | Yes   |
| Short-circuit protection  | Yes   |
| Mains buffering   |   |
| <ul style="list-style-type: none"> <li>Mains/voltage failure stored energy time</li> </ul>  | 10 ms   |
| Input current   |   |
| Current consumption (rated value)   | 350 mA  |
| Current consumption, max.   | 450 mA  |
| Inrush current, max.  | 1 A   |
| I <sup>2</sup> t  | 0.05 A <sup>2</sup> ·s  |
| Power loss  |   |
| Power loss, typ.  | 1.8 W   |
| Address area  |   |
| Address space per module  |   |
| <ul style="list-style-type: none"> <li>Address space per module, max.</li> </ul>  | 288 byte; For input and output data respectively  |
| Address space per station   |   |

|   |   |
|---|---|
| • Address space per station, max.                   | 1 440 byte  |
| <b>Hardware configuration</b>                       |   |
| <b>Rack</b>   |   |
| • Quantity of operable ET 200SP modules, max.       | 32  |
| • Quantity of operable ET 200AL modules, max.       | 16  |
| <b>Submodules</b>                                   |   |
| • Number of submodules per station, max.            | 256   |
| <b>Interfaces</b>                                   |   |
| Number of PROFINET interfaces                       | 1; 2 ports (switch)                               |
| <b>1. Interface</b>                                 |   |
| <b>Interface types</b>                              |   |
| • RJ 45 (Ethernet)                                  | Yes; with BusAdapter                              |
| • Number of ports                                   | 2; with BusAdapter                                |
| • integrated switch                                 | Yes   |
| • BusAdapter (PROFINET)                             | Yes   |
| <b>Protocols</b>                                    |   |
| • PROFINET IO Device                                | Yes   |
| • Open IE communication                             | Yes   |
| • Media redundancy                                  | Yes; PROFINET MRP client                          |
| <b>PROFINET IO Device</b>                           |   |
| <b>Services</b>                                     |   |
| — IRT   | Yes; 1 ms to 4 ms at an interval of 125 µs        |
| — Dynamic Frame Packing (DFP)                       | Yes   |
| — Fast Forwarding                                   | Yes   |
| — Fragmentation                                     | Yes   |
| — PROFIenergy                                       | Yes   |
| — Prioritized startup                               | Yes   |
| — Shared device                                     | Yes   |
| — Number of IO Controllers with shared device, max. | 4   |
| <b>Interface types</b>                              |   |
| <b>RJ 45 (Ethernet)</b>                             |   |
| • Transmission procedure                            | PROFINET with 100 Mbit/s full duplex (100BASE-TX) |
| • 100 Mbps  | Yes   |
| • Autonegotiation                                   | Yes   |
| • Autocrossing                                      | Yes   |
| <b>Protocols</b>                                    |   |
| Supports protocol for PROFINET IO                   | Yes   |
| PROFIsafe   | Yes   |
| PROFIBUS  | No  |
| EtherNet/IP   | No  |
| Modbus TCP  | No  |
| <b>Redundancy mode</b>                              |   |
| • PROFINET system redundancy (S2)                   | No  |
| <b>Media redundancy</b>                             |   |
| — MRP   | Yes   |
| — MRPD  | No  |
| <b>Open IE communication</b>                        |   |
| • TCP/IP  | Yes   |
| • UDP   | Yes   |
| • SNMP  | Yes   |
| • LLDP  | Yes   |
| • ARP   | Yes   |
| • IGMP  | Yes   |
| • Multicast   | Yes   |
| • Broadcast   | Yes   |
| • IPv4  | Yes   |
| • IPv6  | No  |
| <b>Interrupts/diagnostics/status information</b>    |   |
| Status indicator                                    | Yes   |
| Alarms  | Yes   |

|  |   |
|--|---|
| Diagnostics function   | Yes   |
| <b>Diagnostics indication LED</b>  |   |
| • RUN LED  | Yes; green LED  |
| • ERROR LED  | Yes; red LED  |
| • MAINT LED  | Yes; Yellow LED   |
| • Monitoring of the supply voltage (PWR-LED)   | Yes; green PWR LED  |
| • Connection display LINK TX/RX  | Yes; 2x green link LEDs on BusAdapter   |
| <b>Potential separation</b>  |   |
| between backplane bus and electronics  | No  |
| between PROFINET and all other circuits  | Yes; 1500 V AC (type test)  |
| between supply and all other circuits  | No  |
| <b>Permissible potential difference</b>  |   |
| between different circuits   | Safety extra low voltage SELV   |
| <b>Isolation</b>   |   |
| Isolation tested with  | 707 V DC (type test)  |
| <b>Standards, approvals, certificates</b>  |   |
| Network loading class  | 3   |
| <b>product functions / security / header</b>   |   |
| PROFINET Security Class  | 1   |
| signed firmware update   | Yes   |
| safely removing data   | Yes   |
| data integrity   | Yes   |
| <b>Ambient conditions</b>  |   |
| <b>Ambient temperature during operation</b>  |   |
| • horizontal installation, min.  | -40 °C; = Tmin (incl. condensation/frost)   |
| • horizontal installation, max.  | 70 °C; = Tmax; +85 °C for 10 min (OT4, ST1/ST2 acc. to EN 50155)  |
| • vertical installation, min.  | -40 °C; = Tmin  |
| • vertical installation, max.  | 50 °C; = Tmax   |
| <b>Altitude during operation relating to sea level</b>                                       |   |
| • Installation altitude above sea level, max.  | 5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual  |
| <b>Relative humidity</b>   |   |
| • With condensation, tested in accordance with IEC 60068-2-38, max.                          | 100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation   |
| <b>Resistance</b>  |   |
| <b>Coolants and lubricants</b>   |   |
| — Resistant to commercially available coolants and lubricants                                | Yes; Incl. diesel and oil droplets in the air   |
| <b>Use in stationary industrial systems</b>  |   |
| — to biologically active substances according to EN 60721-3-3                                | Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request  |
| — to chemically active substances according to EN 60721-3-3                                  | Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *  |
| — to mechanically active substances according to EN 60721-3-3                                | Yes; Class 3S4 incl. sand, dust, *  |
| — Against mechanical environmental conditions acc. to EN 60721-3-3                           | Yes; Class 3M8 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0/6AG1193-6AB00-0AA0)   |
| <b>Use on ships/at sea</b>   |   |
| — to biologically active substances according to EN 60721-3-6                                | Yes; Class 6B2 mold, fungal and dry rot spores (excluding fauna)  |
| — to chemically active substances according to EN 60721-3-6                                  | Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *  |
| — to mechanically active substances according to EN 60721-3-6                                | Yes; Class 6S3 incl. sand, dust; *  |
| — Against mechanical environmental conditions acc. to EN 60721-3-6                           | Yes; class 6M4 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0/6AG1193-6AB00-0AA0)   |
| <b>Usage in industrial process technology</b>  |   |
| — Against chemically active substances acc. to EN 60654-4                                    | Yes; Class 3 (excluding trichlorethylene)   |
| — Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04 | Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil) |
| <b>Remark</b>  |   |
| — Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and | * The supplied plug covers must remain in place over the unused interfaces during operation!  |

ANSI/ISA-71.04

| Conformal coating   |  |
|---|--|
| • Coatings for printed circuit board assemblies acc. to EN 61086  | Yes; Class 2 for high reliability                          |
| • Protection against fouling acc. to EN 60664-3   | Yes; Type 1 protection                                     |
| • Military testing according to MIL-I-46058C, Amendment 7   | Yes; Discoloration of coating possible during service life |
| • Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A | Yes; Conformal coating, Class A                            |

| connection method |                            |
|-------------------|----------------------------|
| ET-Connection     |                            |
| • via BU/BA Send  | Yes; + 16 ET 200AL modules |

| Mechanics/material |               |
|--------------------|---------------|
| Strain relief      | Yes; Optional |

| Dimensions |        |
|------------|--------|
| Width      | 50 mm  |
| Height     | 117 mm |
| Depth      | 74 mm  |

| Weights         |                           |
|-----------------|---------------------------|
| Weight, approx. | 125 g; without BusAdapter |

| Classifications |        |         |                |
|-----------------|--------|---------|----------------|
|                 |        | Version | Classification |
|                 | eClass | 14      | 27-24-26-08    |
|                 | eClass | 12      | 27-24-26-08    |
|                 | eClass | 9.1     | 27-24-26-08    |
|                 | eClass | 9       | 27-24-26-08    |
|                 | eClass | 8       | 27-24-26-08    |
|                 | eClass | 7.1     | 27-24-26-08    |
|                 | eClass | 6       | 27-24-26-08    |
|                 | ETIM   | 9       | EC001604       |
|                 | ETIM   | 8       | EC001604       |
|                 | ETIM   | 7       | EC001604       |

| Approvals / Certificates |                      |
|--------------------------|----------------------|
| General Product Approval | Maritime application |

[Miscellaneous](#)

[Manufacturer Declaration](#)



last modified:

7/3/2025