



Combinations for connectors in Gel filled boxes

SC-4 0525-S

E1441332

Splicing Connector, 2-Pole, 0.5-2.5mm², AWG 20-14, with Lever, Red/Black



Product Properties:

Number of clamp positions (device side)	4 .
Type of locking/unlocking	Lever
Nominal voltage	450 V
Nominal current	32 A
Suitable for solid conductors	Yes
Transparent	Yes
Number of clamp positions	4 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Strip length	12 mm
Colour	Green, Multi-coloured
Operating temperature	-40-105 °C
Connector type	Splicing connector
Flammability rating (UL94)	V2

Dimensions:

Max. AWG-size	14
Min. AWG-size	20
Nominal cross section (device side)	0.5-2.5 mm ²
Nominal cross section (installation side)	0.5-2.5 mm ²

Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.5-2.5 mm ²
Conductor cross section solid (solid, stranded)	0.5-4 mm ²
Width	90 mm
Height	11 mm
Strip length	12 mm
MOQ	50 .
Unit	pcs
Nominal cross section	0.5-2.5 mm ²
Length	25 mm
Nominal voltage	450 V

Approvals:

Approved according to CE	Yes
Approved according to TUV	Yes
Approved according to UKCA	Ja

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	In compliance
PFAS	No PFAS
POPs	No POPs
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS

Other information:

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	102014
Search Description	ENR2023H SKV2024ERIK2
Alternative SKU	SC-40525-S
E-no	E1441332

Logistic information:

Barcode	733117612184
Country of origin	CN
E-no	E1441332
Item status	Stock item, normally in stock with reservation for in between sales.

MOQ	50 .
Stock code	SC-4 0525-S
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.

Nelco Contact AB - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - order@nelco.se - www.nelco.se