



Heavy-Duty 1-1/8" SDS Rotary Hammer Kit With Chipping Feature - DW570K

FEATURES

- 8.3 Amp motor provides high performance and overload protection.
- Hard-hitting hammer mechanism for fast and efficient penetration.
- Fully sealed gearbox engineered for long life by keeping grease in and dust out.
- Accepts SDS bits from 5/32" to 1-1/8"
- Higher drilling capacity than compact drilling hammers for increased productivity in 1/2" & larger applications.
- Less weight than large drilling hammers reduces user fatigue in 5/8" & smaller applications.
- Chipping (Hammer-Only) mode allows user to perform light chipping applications.
- Rotation-only mode for wood and metal drilling (using SDS-to-Round Shank Adapter).
- Dual wall housing construction with rubber mounts between isolates vibration to inner housing. This reduces user-felt vibration causing less fatigue.
- Variable speed allows for precise hole placement.
- Multiple O-rings and dust seals prevent dust from entering the tool for extended hammer mechanism life.
- Factory-set clutch reduces sudden, high-torque reactions if bit jams.
- 360° Side Handle is easily adjustable for user preference or use in tight spaces.
- Removable / replaceable chuck allows quick installation of 1/2" round shank chuck and permits easier service.
- Modular design provides easy access to switch, cordset, brushes, motor and gear case for ease of service.
- Switch and brushes designed for long life in dusty, contaminated environments.

SPECIFICATIONS

Amps	8.3 Amps
Switch	VS
Concrete Drilling	1 1/8 "
Chipping	Yes
Wood/Steel Drilling	1.5 / .5 "
No Load Speed	0-730 rpm
Blows/Min	0-4,100 bpm
Impact Energy	3.34 ft/lbs
Clutch	Yes
Tool Length	15.25 "
Tool Weight	10.75 lbs