



Fuse-link, low voltage, 100 A, AC 660 V, DC 460 V, 80 kA, BS88/A4, 26 x 110 mm, gM, BS, motor-rated



Part no. **100M125 AMP 660V AC FUSE**
 Catalog No. **TCP100M125A**

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	100
Motor current rating	I	A	100M125
Rated voltage			AC 660 V DC 460 V
Construction size			BS88/A4
Size			26 x 110 mm
Utilization category			gM
Description			motor-rated
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			offset bolted tags (slotted)
Standards/Regulations			BS88-2 IEC 60269-2
Optional accessories			fuse-holder RS100

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / HRC fuse (EC004556)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Safety fuse inserts (unspecified) (ecl@ss10.0.1-27-14-20-90 [BAB264011])			
Fuse construction type according to IEC 60269			A4
Type of current			AC/DC
Rated voltage AC		V	660
Rated voltage DC		V	460
Rated current		A	100
Utilization category			gM (motor protection)
Breaking capacity		kA	80
Colour code			None
Type of fuse status indicator			None
Power loss at rated current		W	
Mounting holes			M8
Centre-to-centre distance of connections		mm	93.7