




Get .64 Connector System

TE Internal #: 1-1411325-3
6 Position Housing, Housing for Female Terminals, Wire-to-Board,
2.54 mm [.1 in] Centerline, Brown, Wire & Cable, Signal, Get .64
Connector System

[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Housings > GET .64 CONNECTOR SYSTEM, CONNECTOR HSG



Number of Positions: 6
Connector & Housing Type: **Housing for Female Terminals**
Mating Tab Width: **.64 mm [.02 in]**
Connector System: **Wire-to-Board**
Centerline (Pitch): **2.54 mm [.1 in]**

[All GET .64 Connector System, Connector HSG \(62\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Board
Sealable	No
Primary Locking Feature	On the Terminal
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	6
Number of Rows	2

Body Features

Cable Exit Angle	180°
------------------	------



Primary Product Color	Brown
Connector & Keying Code	C

Contact Features

Contact Size	.64mm
Contact Type	Receptacle
Mating Tab Width	.64 mm[.02 in]

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	Yes
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Product Width	17.75 mm[.698 in]
Row-to-Row Spacing	2.54 mm[.1 in]
Product Length	13.47 mm[.53 in]
Connector Height	22.6 mm[.889 in]

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Tray
Packaging Quantity	160

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1419158-5
MARKT2X3SWIT CONN.B




TE Part # 1-1411224-3
2X3POS. GET-SOCKET HOUSING


Also in the Series | **Get .64 Connector System**




Automotive Connector Caps & Covers (5)



Automotive Headers(3)




Automotive Housings(87)




Automotive Terminals(28)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(3)



Wire-to-Board Headers & Receptacles (3)

Customers Also Bought



TE Part #1452842-3
22 POS FEMALE HSG ASSY




TE Part #CAT-G3353-CH8172
GET .64 CONNECTOR SYSTEM,
CONNECTOR HSG



TE Part #2-2236706-2
2-POS. SEALED 2.8MM USCAR
CLEAN BODY FOR



TE Part #6-967587-3
6POS MQS TAB SEALED COD B




TE Part #213843-2
POWERBAND SKT ASY,8-10,STRIP



TE Part #1-2208709-1
91POS, MIXED,REC HSG,ASSY,
SEALED



TE Part #1-936059-1
2.8MM SLD 2P PLUG ASSY



TE Part #213900-1
CPC SEAL ASSY KIT,SRS 6,17-10



TE Part #1452839-5
24 POS FEMALE HSG ASSY

Documents

Product Drawings

2X3POS. GET-ASSY SOCKET HOUSIN

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1411325-3_D.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1-1411325-3_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1411325-3_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[GET 0.64 Interconnection System](#)

English