

HSC1008R0F

✓ ACTIVE

CGS | CGS HS

TE Internal #: 2176297-4


8 ohm, Wire Wound, 1 %, Power Resistor, 100 W, 2 Terminations,
±50 ppm/°C, Solder Lug, Loose Piece - Box, 26 mm [1.024 in]

Height, CGS HS

[View on TE.com >](#)



Passive Components > Resistors > Chassis Mount Resistors



Resistor Type: **Power Resistor**
Resistance Class: **Up to 1kΩ**
Resistance Value: **8 Ω**
Power Rating: **100 W**
Element Type: **Wire Wound**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	1900 VDC
Resistance Class	Up to 1kΩ
Resistance Value	8 Ω
Power Rating	100 W
Passive Component Tolerance	1 %

Termination Features

Number of Terminations	2
Chassis Mount Resistor Termination Type	Solder Lug



Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
--------------------------	----------------------------

Dimensions

Product Height	26 mm[1.024 in]
Product Length	87.5 mm[3.445 in]
Product Width	47.5 mm[1.87 in]

Usage Conditions

Temperature Coefficient	±50 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts



TE Part # 2176297-5
HSC100 70K 5%

TE Part # 2176297-1
HSC100 100R 5% MOQ 2000



TE Part # 2176297-3
HSC100 4R0 1%


Also in the Series | CGS HS



Automotive Housings(1)



Automotive Signal & Power Connector Housings(1)



Card Edge Connector Housings(1)



Chassis Mount Resistors(1069)



FFC Connectors(1)

Customers Also Bought



TE Part #CAT-D48-ST273
DEUTSCH Connector Solid Contacts



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



Documents

Product Drawings

HSC100 8R0 1!%

English

CAD Files

Customer View Model

ENG_CVM_CVM_2176297-4_BA1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2176297-4_BA1.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2176297-4_BA1.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Aluminium Housed Power Resistors - Type HS Series

English