

## Selector switch, 1N/O, 2 positions, front mount

Part no. M22-WRK/K10 Article no. 216518 Powering Business Worldwide

Catalog No. M22-WRK-K10Q

# **Delivery programme**

Product range

Basic function Single unit/Complete unit Description

Function Function Contacts

N/O = Normally open Contact sequence  $RMQ\mbox{-}Titan$  (drilling dimensions 22.5 mm)

Selector switch actuators Complete unit

Thumb-gripcolour black Stay-put/spring-return function, can be

changed with coding parts M22-XC-Y 2 positions, maintained

Stay-put 1 N/0

Bezel: Silver

Front ring

Connection to SmartWire-DT

#### Notes

Switch positions 0, I and II correspond with the position of the actuator as viewed from the front.

## **Approvals**

Product Standards UL File No. UL Category Control No. CSA File No. CSA Class No.

North America Certification Degree of Protection

IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking

E29184 NKCR 012528 3211-03

UL listed, CSA certified UL/CSA Type 3R, 4X, 12, 13

IEC/ENI COO47

# General

Standards

Lifespan, mechanical

Operating frequency

Operating torque (screw terminals)

Protection type

Climatic proofing

Ambient temperature

Open

Mounting position

Mechanical shock resistance

		IEC/EN 60947 VDE 0660
Operations	x 10 <sup>6</sup>	> 0.1
Operations/ h		≦ <sub>2000</sub>
	Nm	≦ <sub>0.3</sub>
		IP66
		Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
	°C	
	°C	- 25 - + 70
		As required
	g	30 Shock duration 11 ms Sinusoidal according to IEC 60068-2-27

#### **Technical data ETIM 5.0**

Low-voltage industrial components (EG000017) / Selector switch, complete (EC001029)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Selector switch, complete unit (ecl@ss8-27-37-12-43 [ACN984007])

(ecl@ss8-27-37-12-43 [ACN984007])		
Number of switch positions		2
Type of control element		Toggle
Suitable for illumination		No
With lamp		No
Colour button		Black
Hole diameter	mm	22
Width opening	mm	0
Height meter opening	mm	0
Switching function latching		Yes
Spring-return Spring-return		No
Degree of protection (IP)		IP66
Supply voltage	V	0 - 0


Number of contacts as normally open contact
Number of contacts as normally closed contact
Number of contacts as change-over contact
Type of electric connection
With front ring
Material front ring


0

Screw connection Yes Plastic Chrome

## **Dimensions**

Colour front ring





# **Additional product information (links)**

IL04716002Z (AWA1160-1745) RMQ-Titan System

IL04716002Z (AWA1160-1745) RMQ-Titan System ftp://ftp.moeller.net/D0CUMENTATION/AWA\_INSTRUCTIONS/IL04716002Z2013\_08.pdf