



## VESTA+ - S2

Réf. : 15113



|                                          |                                                                                    |
|------------------------------------------|------------------------------------------------------------------------------------|
| <b>Suitable for :</b>                    | Inside                                                                             |
| <b>Type :</b>                            | Low shoe                                                                           |
| <b>Activity :</b>                        | Food industry, Catering, Medical / Chemical Industry                               |
| <b>Upper :</b>                           | Dry-Tek® material ,thickness 2.2 mm, acid resistant, washable and breathable       |
| <b>Lining :</b>                          | Cambrelle Amicor+® with Refreshing microcells perfume system                       |
| <b>Tongue :</b>                          | Dry-Tek® material                                                                  |
| <b>Ankle protection :</b>                |                                                                                    |
| <b>Fastening :</b>                       | Pull on style with elastique strap                                                 |
| <b>Toe cap :</b>                         | Composite 200 joules Light System®                                                 |
| <b>Midsole :</b>                         |                                                                                    |
| <b>Insole :</b>                          | Antibacterial and antimicrobial foam                                               |
| <b>Sole :</b>                            | PU 2D, oil resistant FO, antistatic and HI-CI insulated                            |
| <b>Sole pattern :</b>                    | Special non-slip crampons for smooth and greasy floors, SRC standard               |
| <b>Weight (Kg/pair) :</b>                | 0.800                                                                              |
| <b>Colors :</b>                          | Black upper and dark grey/black outsole                                            |
| <b>Sizes :</b>                           | 35-48 (2-13)                                                                       |
| <b>Standard :</b>                        | EN ISO 20345:2011 SRC                                                              |
| <b>CE certificate of conformity N° :</b> | 0075/020/161/04/13/0269 - EXT 01/04/13                                             |
| <b>Special features :</b>                | Upper without side stitching: no water infiltration risks                          |
| <b>Special features 2 :</b>              | Dry-Tek® material resistant to 12 acids and corrosive fluids (standard EN 13832-2) |
| <b>Special features 3 :</b>              | Washable up to 60°C                                                                |

### SPECIAL FEATURES

-  200 joules light composite toecap
-  Metal free, non magnetic
-  Water absorption and penetration resistance of upper (WRU)

**Cambrelle+**  
with  
Amicor+  
PLUS

### GENERAL FEATURES

|                                                                                     |                                   |     |     |
|-------------------------------------------------------------------------------------|-----------------------------------|-----|-----|
|  | Antistatic properties (A)         | YES | YES |
|  | Heel energy absorption (E)        | YES | YES |
|  | Abrasion resistance               | YES | YES |
|  | Crampon sole                      | YES | YES |
|  | Heat-insulated sole (HI)          | YES | YES |
|  | Cold-insulated sole (CI)          | YES | YES |
|  | 200 joule extra-wide toecap       | YES | YES |
|  | Hyper-ventilated lining           | YES | YES |
|  | Perforation-resistance 1100 N (P) | YES | YES |