




PRODUCT-DETAILS

AF265-30-00-34

AF265-30-00-34 Contactor



General Information	
Extended Product Type	AF265-30-00-34
Product ID	1SFL547002R3400
EAN	7320500504697
Catalog Description	AF265-30-00-34 Contactor
Long Description	The AF265-30-00-34 is a 3 pole - 1000 V IEC or 600 V UL contactor with Main Circuit Bars, controlling motors up to 132 kW / 400 V AC (AC-3) or 200 hp / 480 V UL and switching power circuits up to 400 A (AC-1) or 350 A UL general use. Thanks to the AF technology, the contactor has a wide control voltage range (250-500 V 50/60 Hz and DC), managing large control voltage variations, reducing panel energy consumptions and ensuring distinct operations in unstable networks. Furthermore, surge protection is built-in, offering a compact solution. AF contactors have a block type design, can be easily extended with add-on auxiliary contact blocks and an additional wide range of accessories. Includes Mounting kit, containing all neccessary screws, washers and sockets for connecting the terminals, and screws for mounting the device.

Ordering	
Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Popular Downloads

EPLAN Data	9AAC175202_EPLAN
Data Sheet, Technical Information	1SBC100214C0202
Data Sheet, Technical Information (Part 2)	1SAC200017M0002
Instructions and Manuals	1SFC100008M0201
CAD Dimensional Drawing	2CDC001079B0201

Dimensions

Product Net Width	140 mm
Product Net Depth / Length	195.5 mm
Product Net Height	225 mm
Product Net Weight	3.9 kg

Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	0
Number of Auxiliary Contacts NC	0
Number of Poles	3P
Rated Operational Voltage	Main Circuit 1000 V
Rated Frequency (f)	Main Circuit 50 Hz Main Circuit 50 / 60 Hz
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-4-1, Open Contactors $\Theta = 40\text{ °C}$ 400 A
Rated Operational Current AC-1 (I_e)	(1000 V) 40 °C 350 A (1000 V) 60 °C 300 A (1000 V) 70 °C 240 A (690 V) 40 °C 400 A (690 V) 70 °C 290 A
Rated Operational Current AC-3 (I_e)	(415 V) 55 °C 265 A (440 V) 55 °C 265 A (500 V) 55 °C 250 A (690 V) 55 °C 250 A (1000 V) 55 °C 113 A (380 / 400 V) 55 °C 265 A (220 / 230 / 240 V) 55 °C 265 A
Rated Operational Power AC-3 (P_e)	(415 V) 132 kW (440 V) 160 kW (500 V) 160 kW (690 V) 200 kW (1000 V) 160 kW (380 / 400 V) 132 kW (220 / 230 / 240 V) 75 kW
Rated Breaking Capacity AC-3	8 x I_e AC-3
Rated Breaking Capacity AC-3e	8.5 x I_e AC-3e

Rated Making Capacity AC-3	10 x Ie AC-3
Rated Making Capacity AC-3e	12 x Ie AC-3e
Short-Circuit Protective Devices	gG Type Fuses 500 A
Rated Short-time Withstand Current Low Voltage (I_{cw})	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 400 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 1224 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 2650 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 2120 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 865 A
Rated Insulation Voltage (U_i)	acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V acc. to UL/CSA 600 V
Rated Impulse Withstand Voltage (U_{imp})	8 kV Main Circuit 8 kV
Maximum Electrical Switching Frequency	(AC-1) 300 cycles per hour (AC-2 / AC-4) 150 cycles per hour (AC-3) 300 cycles per hour
Mechanical Durability	5 million
Maximum Mechanical Switching Frequency	300 cycles per hour
Coil Operating Limits	(acc. to IEC 60947-4-1) 0.85 x U_c Min. ... 1.1 x U_c Max. (at $\theta \leq 70$ °C)
Rated Control Circuit Voltage (U_c)	50 Hz 250 ... 500 V 60 Hz 250 ... 500 V DC Operation 250 ... 500 V
Coil Consumption	Holding at Max. Rated Control Circuit Voltage 50 Hz 20.4 V-A Holding at Max. Rated Control Circuit Voltage 60 Hz 20.4 V-A Pull-in at Max. Rated Control Circuit Voltage 50 Hz 550 V-A Pull-in at Max. Rated Control Circuit Voltage 60 Hz 550 V-A Pull-in at Max. Rated Control Circuit Voltage DC 650 V-A Pull-in at Max. Rated Control Circuit Voltage DC 650 W
Power Loss	at Rated Operating Conditions per Pole 14 W
Operate Time	Between Coil De-energization and NO Contact Opening 37 ... 47 ms Between Coil Energization and NO Contact Closing 25 ... 55 ms
Connecting Capacity Main Circuit	Flexible 2 x 70 ... 185 mm ² Rigid Cu-Cable 2 x 70 ... 185 mm ²
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 ... 2.5 mm ² Flexible 2x0.75 ... 2.5 mm ² Solid 2 x 1 ... 4 mm ² Stranded 2 x 1 4 mm ²
Connecting Capacity	Flexible 2 x 70 ... 185 mm ² Rigid Cu-Cable 2 x 70 ... 185 mm ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP40 acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP00
Tightening Torque	Cable Lug 9 N-m Main Circuit 22 ... 43 N-m
Terminal Type	Main Circuit: Bars
Product Name	Block Contactor

Technical UL/CSA

NEMA Size	5
Continuous Current Rating NEMA	270 A
Horsepower Rating NEMA	(200 V AC) Three Phase 75 Hp (230 V AC) Three Phase 100 Hp (460 V AC) Three Phase 200 Hp (575 V AC) Three Phase 200 Hp
Maximum Operating	Main Circuit 600 V

Voltage UL/CSA

General Use Rating UL/CSA	(1000 V AC) 350 A
------------------------------	-------------------

Horsepower Rating UL/CSA	(200 ... 208 V AC) Three Phase 40 Hp (200 V AC) Three Phase 75 hp (208 V AC) Three Phase 75 hp (220 ... 240 V AC) Three Phase 40 Hp (220 ... 240 V AC) Three Phase 100 hp (440 ... 480 V AC) Three Phase 100 Hp (440 ... 480 V AC) Three Phase 200 hp (550 ... 600 V AC) Three Phase 125 Hp (550 ... 600 V AC) Three Phase 250 hp
-----------------------------	---

Environmental

Ambient Air Temperature	Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc) -25 ... 55 ° C Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc) -25 ... 50 ° C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... 70 °C Close to Contactor for Storage -40 ... 70 °C
Maximum Operating Altitude Permissible	Without Derating 3000 m

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS Declaration	2CMT2021-006277
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006525
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

ABB EcoSolutions

ABB EcoSolutions	Yes
ABB Site Meeting Group Waste To Landfill Target	Non-hazardous waste is sent to a landfill, where there is no alternative option available within 100km of a facility
End Of Life Disassembling Instructions	1SFC100112M0002
Environmental Product Declaration - EPD	1SFC100104D0201
Improved Energy Efficiency for Customers	Product Efficiency - Product considered more energy-efficient compared to similar product on market or older products from the same line
Recyclability Rate of the Product acc. to EN45555	Design for Closing Resource Loops - Standard EN45555 - 76.3 %
Sustainable Material Content in Product (wt. %)	Recycled Metal - 33 %

Certificates and Declarations

A2L Certificate – UL	9AKK108468A6695
----------------------	-----------------

ABS Certificate	14-LD1092198-PDA
BV Certificate	BV_36353_AOBV
CB Certificate	SE-89316
CCS Certificate	GB14T00030
CQC Certificate	CQC2014010304676670 CQC2014010304673866
Declaration of Conformity - CCC	2020980304001305 2020980304001068
Declaration of Conformity - CE	2CMT2015-005439
Declaration of Conformity - UKCA	2CMT2020-006118
DNV Certificate	DNV_E-14043
EAC Certificate	9AKK107046A8618
GL Certificate	GL_95073-14HH
LR Certificate	LR_14_70011(E1)
PRS Certificate	TE_2092_880423_16
RINA Certificate	ELE060313XG_002
RMRS Certificate	9AKK107045A6978
UL Certificate	20121217-E36588
UL Listing Card	UL_E36588

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	263 mm
Package Level 1 Depth / Length	203 mm
Package Level 1 Height	289 mm
Package Level 1 Gross Weight	4.6 kg
Package Level 1 EAN	7320500504697

External Classifications and Standards

Object Classification Code	Q
ETIM 7	EC000066 - Power contactor, AC switching
ETIM 8	EC000066 - Power contactor, AC switching
ETIM 9	EC000066 - Power contactor, AC switching
eClass	V11.0 : 27371003
UNSPSC	39121529
IDEA Granular Category Code (IGCC)	4758 >> Iec Contactors
E-Number (Finland)	3707519

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors → AF Contactors → AF265


The ABB Eco Solutions logo. It features a red horizontal bar above the text "ABB" in a sans-serif font. Below "ABB" is the word "Eco" in a large, bold, sans-serif font, and "Solutions™" in a smaller, bold, sans-serif font below it.

ABB
Eco
Solutions™