

天溯
Tian Su



深圳天溯计量检测股份有限公司
ShenZhen Tiansu Calibration and Testing Co., Ltd.



中国认可
国际互认
检测
TESTING
CNAS L5138

Rep.No.:TCTTJ20210307246ZB-BR01

Page 1 / 15 Pages

检测报告 UN38.3

Name of sample:

Polymer Lithium-ion Battery

产品名称:

聚合物锂离子电池

Client:

Dongguan Lirui Electronics Co., Ltd.

委托单位:

东莞市锂锐电子有限公司

Classification:

Commission Test

检测类别:

委托测试

Shenzhen Tiansu Calibration and Testing Co.,Ltd
深圳天溯计量检测股份有限公司

B/1,4, NO.2 Jinlong Road, Longgang District, Shenzhen, China
深圳市龙岗区宝龙街道锦龙大道 2 号 1 栋、4 栋

Web: www.tiansu.org

E-mail: tsjc@tiansu.org

Tel: 0755-89457984

UN38.3



TS(SZ)-J3-001-001-A1

Rep. No.: TCTTJ20210307246ZB-BR01

Page 2 / 15 Pages

Name of samples: Polymer Lithium-ion Battery 样品名称: 聚合物锂离子电池	Trade mark: - 商标: -
Commissioned by: Dongguan Lirui Electronics Co., Ltd. 委托单位: 东莞市锂锐电子有限公司	Commissioner address: Floor 3, Building A, No.5, Huanwei Street, Fugang Village, Qingxi Town, Dongguan city 委托单位地址: 东莞市清溪镇浮岗村环卫街 5 号 A 栋 3 楼
Manufacturer by: Dongguan Lirui Electronics Co., Ltd. 制造单位: 东莞市锂锐电子有限公司	Manufacturer address: Floor 3, Building A, No.5, Huanwei Street, Fugang Village, Qingxi Town, Dongguan city 制造单位地址: 东莞市清溪镇浮岗村环卫街 5 号 A 栋 3 楼
Manufacturer's Contact Information 制造商联系信息: Phone:0769-82867929 Email:1291853173@qq.com	Manufacturer's Web Site 制造商网址:
Type/Model 型号规格: 801525	shape: Prismatic 样品形状: 棱形
Appearance color: Silver 样品颜色: 银色	Sample size 样品尺寸: T(12.45mm)*W(20.02mm)*L(31.54mm)
Rated info. 额定信息: 3.7V/240mAh/0.888Wh	Cell quantity 组成电芯数量: 1PCS
Quantity of sample: 30cells+18batteries 样品数量: 30 个电芯+18 个电池	Cell model 电芯型号: 801525
Limited charge voltage 充电限制电压: 4.2V	Cut-off voltage 放电截止电压: 3.0V
Standard charge current 标准充电电流: 48mA	Max continuous charge current 最大持续充电电流: 240mA
Standard discharge current 标准放电电流: 48mA	Max continuous discharge current 最大持续放电电流: 240mA
Receiving date 接样日期: 2021.3.5	Sample identification 样品标识序号: B1#~B18#,C1#~C30#
Completing date 完成日期: 2021.3.16	Test item: 8 items 测试项目: 8 项
Test conclusion: 检测结论: The Polymer Lithium-ion Battery submitted by Dongguan Lirui Electronics Co., Ltd are tested according to Section 38.3 of the Sixth Revised Edition Amendment 1 of the Recommendations on the Transport of Dangerous Goods, Manual of Test and Criteria (ST/SG/AC.10/11/Rev.6/Amend.1/Section38.3). The test results comply with the relevant requirements of the standard. 由东莞市锂锐电子有限公司送检的聚合物锂离子电池, 依据《关于危险品货物运输的建议书》试验和标准手册第六修订版修正 1 第 38.3 节进行检测, 测试结果符合标准相关要求。	
Date of issue: March 17, 2021 签发日期: 2021 年 3 月 17 日	

批准\Approved by
技术负责人\
Technology Supervisor

审核\Reviewed by
项目工程师\
Project Engineer

主检\Tested by
测试工程师\
Test Engineer

刘澳

刘澳

Description and illustration of the sample:

样品说明及描述:

Test item 测试项目	Sample No. 样品编号	State 状态	Remark 备注
T.1~T.5	B1#~B5#	at first cycle in fully charged states; 在第一个循环完全充电;	Battery 电池
	B6#~B10#	after 25 cycles ending in fully charged states; 在第二十五个循环完全充电;	
T.6	C1#~C5#	at first cycle at 50% of the design rated capacity; 在第一个循环充电 50%的额定容量;	Cell 电芯
	C6#~C10#	after 25 cycles ending in fully charged at 50% of the design rated capacity; 在第二十五个循环充电 50%的额定容量;	
T.7	B11#~B14#	at first cycle in fully charged states; 在第一个循环完全充电;	Battery 电池
	B15#~B18#	after 25 cycles ending in fully charged states; 在第二十五个循环完全充电;	
T.8	C11#~C20#	at first cycle in fully discharged states; 在第一个循环完全放电;	Cell 电芯
	C21#~C30#	after 25 cycles ending in fully discharged states; 在第二十五个循环完全放电;	

Description of the sampling procedure:

取样程序的说明:

N/A

Description of report revision :

报告修订的说明:



Remarks:

备注:



The Polymer Lithium-ion Battery submitted by Dongguan Lirui Electronics Co., Ltd are single cell batteries.

由东莞市锂电电子有限公司所送的聚合物锂离子电池是单电芯电池。

Photos of Battery\电池图片



Photos of Cell 电芯图片



38.3.4	Procedure/测试步骤					—	
38.3.4.1	Test 1: Altitude simulation/测试 1：高度模拟					P	
	Test cells and batteries shall be stored at a pressure of 11.6kPa or less for at least six hour at ambient temperature (20±5℃) . 将电芯和电池在温度为 20±5℃，大气压力为不大于 11.6kpa 的环境中贮存不少于 6 个小时。						
	Requirement/标准要求： 1.Cells and batteries Mass loss limit: ≤0.2% . 样品质量损失≤0.2%。 2.Open circuit voltage not less than 90%, The requirement relating to voltage is not applicable to test cells and batteries at full discharged states. 样品试验后开路电压应不低于试验前开路电压的 90%,此要求不适用于完全放完电的电池和电芯。 3.No leakage, no venting, no disassembly, no rupture and no fire. 样品（电池）应无漏液、无排气、无解体、无破裂以及无着火现象的发生。						
	Result 测试结果						
Sample No. 样品编号	Before test 测试前		After Test 测试后		Mass loss 质量损失(%)	Residual OCV 剩余电压(%)	Test result 测试结果
	Mass 样品质量 (g)	Voltage 开路电压(V)	Mass 样品质量(g)	Voltage 开路电压(V)			
B1#	4.091	4.179	4.091	4.179	0.00	100.00	P
B2#	4.089	4.165	4.088	4.165	0.02	100.00	P
B3#	4.089	4.176	4.089	4.176	0.00	100.00	P
B4#	4.076	4.163	4.076	4.162	0.00	99.98	P
B5#	4.089	4.166	4.089	4.166	0.00	100.00	P
B6#	4.076	4.165	4.076	4.165	0.00	100.00	P
B7#	4.075	4.163	4.074	4.163	0.02	100.00	P
B8#	4.079	4.164	4.079	4.164	0.00	100.00	P
B9#	4.092	4.174	4.092	4.174	0.00	100.00	P
B10#	4.085	4.163	4.085	4.162	0.00	99.98	P
Other supplements : Test result "P" decides that the test item passes. 其他补充：测试结果“P”代表判定该测试项目通过。							

38.3.4	Procedure/测试步骤						—
38.3.4.2	Test 2: Thermal test/测试 2：温度测试						P
	Test cells and batteries are to be stored for at least six hours at a test temperature equal to 72±2℃, followed by storage for at least six hours at a test temperature equal to -40±2℃, The maximum time interval between test temperature extremes in 30 minutes, This procedure is to be repeated until 10 total cycles are complete, after which all test cells and batteries are to be stored for 24 hours at ambient temperature (20±5℃). 将电芯和电池在温度为 72±2℃的条件下贮存不少于 6 个小时，然后，在温度-40±2℃条件下贮存不少于 6 个小时，两个温度间的间隔最长为 30min,重复操作上述步骤直到 10 次，然后，将其在环境温度为 20±5℃的条件下放置 24 个小时。						
	Requirement/标准要求： 1.Cells and batteries Mass loss limit: ≤0.2% . 样品质量损失≤0.2%. 2.Open circuit voltage not less than 90%, The requirement relating to voltage is not applicable to test cells and batteries at full discharged states. 样品试验后开路电压应不低于试验前开路电压的 90 % ,此要求不适用于完全放完电的电池和电芯。 3.No leakage, no venting, no disassembly, no rupture and no fire. 样品（电池）应无漏液、无排气、无解体、无破裂以及无着火现象的发生。						
	Result 测试结果						
Sample No. 样品编号	Before test 测试前		After Test 测试后		Mass loss 质量损失(%)	Residual OCV 剩余电压(%)	Test result 测试结果
	Mass 样品质量 (g)	Voltage 开路电压(V)	Mass 样品质量(g)	Voltage 开路电压(V)			
B1#	4.091	4.179	4.089	4.155	0.05	99.43	P
B2#	4.088	4.165	4.086	4.141	0.05	99.42	P
B3#	4.089	4.176	4.087	4.152	0.05	99.43	P
B4#	4.076	4.162	4.074	4.138	0.05	99.42	P
B5#	4.089	4.166	4.087	4.142	0.05	99.42	P
B6#	4.076	4.165	4.074	4.141	0.05	99.42	P
B7#	4.074	4.163	4.072	4.139	0.05	99.42	P
B8#	4.079	4.164	4.077	4.140	0.05	99.42	P
B9#	4.092	4.174	4.090	4.150	0.05	99.43	P
B10#	4.085	4.162	4.083	4.138	0.05	99.42	P
Other supplements : Test result "P" decides that the test item passes.							
其他补充：测试结果“P”代表判定该测试项目通过。							

[illegible]

38.3.4	Procedure/测试步骤					—	
38.3.4.4	Test 4: Shock/测试 4: 冲击					P	
	Test cells and batteries shall be secured to the testing machine, and each shall be subjected to a half-sine shock of peak acceleration of 150gn (or Acceleration(gn)= $\sqrt{\frac{100850}{mass}}$), which is smaller) and pulse duration of 6 milliseconds, large cells and large batteries shall be subjected to a half-sine of peak acceleration of 50gn (or Acceleration(gn)= $\sqrt{\frac{30000}{mass}}$), which is smaller) and pulse duration of 11 milliseconds. Each cell or battery shall be subjected to three shocks in the positive direction followed by three shocks in the negative direction of three mutually perpendicular mounting positions of the cell or battery for a total of 18 shocks. 以稳固的托架固定住每个电芯和电池样品的全部配件表面。对每个电芯或电池以峰值为 150gn（或与$\sqrt{\frac{100850}{mass}}$中的较小值）的半正弦的加速度撞击，脉冲持续 6 毫秒，大型电池和大型电池组须经受最大加速度 50gn（或与$\sqrt{\frac{30000}{mass}}$中的较小值）和脉冲持续时间 11 毫秒的半正弦波冲击。每个电池或电池组须在三个互相垂直的电池安装方位的正方向经受三次冲击，接着在反方向经受三次冲击，总共经受 18 次冲击。						
	Requirement/标准要求: 1.Cells and batteries Mass loss limit: ≤0.2%. 样品质量损失≤0.2%. 2.Open circuit voltage not less than 90%, The requirement relating to voltage is not applicable to test cells and batteries at full discharged states. 样品试验后开路电压应不低于试验前开路电压的 90%,此要求不适用于完全放完电的电池和电芯。 3.No leakage, no venting, no disassembly, no rupture and no fire. 样品（电池）应无漏液、无排气、无解体、无破裂以及无着火现象的发生。						
	Result/测试结果						
Sample No. 样品编号	Before test 测试前		After Test 测试后		Mass loss 质量损失(%)	Residual OCV 剩余电压(%)	Test result 测试结果
	Mass 样品质量 (g)	Voltage 开路电压(V)	Mass 样品质量(g)	Voltage 开路电压(V)			
B1#	4.089	4.155	4.089	4.155	0.00	100.00	P
B2#	4.085	4.141	4.084	4.141	0.02	100.00	P
B3#	4.087	4.152	4.087	4.152	0.00	100.00	P
B4#	4.074	4.137	4.074	4.136	0.00	99.98	P
B5#	4.087	4.142	4.087	4.142	0.00	100.00	P
B6#	4.074	4.141	4.074	4.141	0.00	100.00	P
B7#	4.072	4.139	4.072	4.139	0.00	100.00	P
B8#	4.077	4.139	4.076	4.138	0.02	99.98	P
B9#	4.089	4.150	4.089	4.150	0.00	100.00	P
B10#	4.083	4.138	4.083	4.138	0.00	100.00	P
Other supplements : Test result "P" decides that the test item passes. 其他补充: 测试结果“P”代表判定该测试项目通过。							

38.3.4	Procedure/测试步骤	—
38.3.4.5	Test 5: External short circuit/测试 5：外部短路	P
	The cell or battery to be tested shall be temperature stabilized so that its external case temperature reaches 57±4℃ and then the cell or battery shall be subjected to a short circuit condition with a total external resistance of less than 0.1 ohm at 57±4℃, This short circuit condition is continued for at least one hour after the cell or battery external case temperature has returned to 57±4℃, the cell or battery must be observed for a further six hour for the test to be concluded. 保持试验环境温度稳定在 57±4℃，以使电芯或电池样品外表温度达到 57±4℃，然后，在此温度下，将其正负极用小于 0.1 欧姆的线路短接，待电芯或电池的外表温度恢复到 57±4℃之后再持续 1 小时以上，对电芯或电池必须进一步观察 6 个小时才能下结论。	
	Requirement/标准要求： 1.Cells and batteries meet this requirement if their external temperature does not exceed 170℃； 电芯或电池的外壳温度应不超过 170℃； 2. No disassembly, no rupture and no fire during the test and within six hours after this test. 试验后 6 小时内无解体、无破裂、无起火。	
	Result 测试结果	
Sample No. 样品编号	Max External Temp 样品表面最高温度(℃)	Test result 测试结果
B1#	58.4	P
B2#	57.1	P
B3#	57.8	P
B4#	57.7	P
B5#	57.4	P
B6#	58.3	P
B7#	57.4	P
B8#	57.9	P
B9#	57.5	P
B10#	58.1	P
Other supplements ：Test result "P" decides that the test item passes. 其他补充：测试结果“P”代表判定该测试项目通过。		

38.3.4	Procedure/测试步骤	—
38.3.4.6	Test 6: Crush\Impact/ 测试 6: 挤压(适用) 撞击(不适用)	P
	Crush 挤压 A cell or component cell is to be crushed between two flat surfaces. The crushing is to be gradual with a speed of approximately 1.5 cm/s at the first point of contact. The crushing is to be continued until the first of the three options below is reached. (a) The applied force reaches 13kN±0.78kN; (b) The voltage of the cell drops by at least 100 mV; (c) The cell is deformed by 50% or more of its original thickness. Once the maximum pressure has been obtained, the voltage drops by 100mV or more, or the cell is deformed by at least 50% of its original thickness, the pressure shall be released. 电池芯或组成电池芯在两个平面间挤压。挤压在第一个接触点以约 1.5cm/s 的速度慢慢进行, 直到下面三个选项之一达到为止: (a)作用力达到 13kN±0.78kN; (b)电池芯电压降至少达到 100mV; (c)电池厚度和最初比较变形至少 50%。 一旦达到最大压力, 电压降超过 100 mV 或者电池芯变形超过 50%, 压力应该解除。	
	Impact 撞击 (applicable to cylindrical cells not less than 18mm in diameter) The sample cell or component cell is to be placed on a flat smooth surface. A 15.8 mm ± 0.1 mm diameter, at least 6 cm long, or the longest dimension of the cell, whichever is greater, Type 316 stainless steel bar is to be placed across the centre of the sample. A 9.1 kg ± 0.1 kg mass is to be dropped from a height of 61 ± 2.5 cm at the intersection of the bar and sample in a controlled manner using a near frictionless, vertical sliding track or channel with minimal drag on the falling mass. The vertical track or channel used to guide the falling mass shall be oriented 90 degrees from the horizontal supporting surface. The test sample is to be impacted with its longitudinal axis parallel to the flat surface and perpendicular to the longitudinal axis of the 15.8 mm ± 0.1 mm diameter curved surface lying across the centre of the test sample. Each sample is to be subjected to only a single impact. Cells and component cells meet this requirement if their external temperature does not exceed 170°C and there is no disassembly and no fire during the test and within six hours after this test. (适用于直径不小于 18 毫米的圆柱形电池)将电池或元件电池样品平放在一个平面上, 其纵轴平行于测试台面年, 将一直径为 15.8 mm ± 0.1 mm 的 316 型不锈钢棒横放在电池中心位置。然后, 将一质量为 9.1 kg ± 0.1 kg 的物体从 61±2.5 cm 的高度落向样品。样品在进行试验时, 其外表温度应不超过 170°C。且试验结束后 6 个小时之内, 样品应无解体、无起火现象发生。	
	Requirements/标准要求: 1.Cells and component cells meet this requirement if their external temperature does not exceed 170°C; 电芯的外壳温度应不超过 170°C; 2. No disassembly, no fire during the test and within six hours after this test. 试验后 6 小时内无解体、无起火。	

Result 测试结果			
Sample No. 样品编号	OCV prior to test 试验前电压 (V)	Max External Temp 样品表面最高温度(℃)	Test result 测试结果
C1#	3.816	24.3	P
C2#	3.782	24.3	P
C3#	3.793	23.5	P
C4#	3.822	24.6	P
C5#	3.823	24.2	P
C6#	3.801	24.9	P
C7#	3.809	24.8	P
C8#	3.811	24.4	P
C9#	3.835	23.4	P
C10#	3.796	23.6	P
Other supplements : Test result "P" decides that the test item passes. 其他补充: 测试结果"P"代表判定该测试项目通过。			

38.3.4	Procedure/测试步骤	—
38.3.4.7	Test 7: Overcharge/测试 7: 过度充电 When the manufacturer's recommended charge voltage is not more than 18V, the minimum voltage of the test shall be the lesser of two times the maximum charge voltage of the or 22V, whichever is less. When the manufacturer's recommended charge voltage is more than 18V, the charging voltage of the test shall be 1.2 times maximum charge voltage. The charging current is 2 times of the maximum charging current recommended by the manufacturer. 如果厂家推荐的充电电压不超过 18V, 本测试的最小充电电压应该是两倍的厂家标定最大充电电压或者是 22V, 取其中较小者。如果厂家推荐的充电电压超过 18V, 充电电压应该为 1.2 倍的厂家标定最大充电电压。充电电流为厂家推荐的最大充电电流 2 倍。	P
	Requirements/标准要求: No disassembly and no fire during the test and within seven days after the test. 试验样品在试验中和试验后 7 天内, 应无解体和无起火现象发生。	
	Result 测试结果	
Sample No. 样品编号	OCV prior to test 试验前电压 (V)	Test result 测试结果
B11#	4.179	P
B12#	4.163	P
B13#	4.176	P
B14#	4.163	P
B15#	4.166	P
B16#	4.164	P
B17#	4.163	P
B18#	4.164	P
Other supplements : Test result "P" decides that the test item passes. 其他补充: 测试结果"P"代表判定该测试项目通过。		

STATEMENTS

声 明

1. The test report is invalid without the official stamp of Tiansu.
本报告无检测单位印章无效。
2. Nobody is allowed to photocopy or partly photocopy this test report without written permission of Tiansu.
未经本试验室书面同意，不得部分地复制本报告。
3. The test report is invalid without the signatures of Ratifier, Reviewer and Testing engineer.
本报告无批准人、审核人及鉴定人签名无效。
4. The test report is invalid if altered.
本报告涂改无效。
5. Objections to the test report must be submitted to Tiansu within 15 days.
对检测报告若有异议，应于收到报告之日起十五天内向检测单位提出。
6. The test report is valid for the tested samples only.
本报告仅与送检样品有关。

-----报告结束-----