




Power Double Lock

TE Internal #: 177899-6
Housing, Plug, Crimp, Wire-to-Board / Wire-to-Panel / Wire-to-Wire, UL 94V-0, Power Double Lock, Rectangular Wire & Cable Connectors & Housings

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors > STD Temp Power Double Lock Plug



Connector Product Type: **Housing**
Connector & Housing Type: **Plug**
Termination Method to Wire & Cable: **Crimp**
Connector System: **Wire-to-Board, Wire-to-Panel, Wire-to-Wire**
Contact Retention Within Housing: **Without**

[All STD Temp Power Double Lock Plug \(66\)](#)

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board, Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Signal Positions	0
Number of Power Positions	0
Number of Positions	3
Number of Rows	1

Electrical Characteristics

--	--



Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

Contact Layout	Inline
Contact Type	Receptacle
Contact Retention Within Housing	Without

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Material	Nylon 6/6
Centerline (Pitch)	3.96 mm[.156 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CNR, USR
Compatible With Approved Standards Products	CSA/C22.2 No. 182.3-M1987, UL 1977
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	400
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant




China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2238096-1 AMP POWER DBL LOCK CONN, REC. CONTACT	 TE Part # 179593-1 AMP POWER D/LOCK RECCONT. L/P	 TE Part # 179592-2 POWER D/LOCK REC CONT. H/P L/P	 TE Part # 179592-1 AMP POWER D/LOCK REC CONT. L/P
 TE Part # 1-179844-6 PDL 2P HDR 7.92 SR V/T ASSY BLU	 TE Part # 179851-6 AMP POWER D/LOCK TAB HDR 3P V	 TE Part # 177907-6 POWER DBL LOCK CAP HSG P/M 3P	 TE Part # 179464-6 AMP POWER DBL LOCK CAP HSG 3P




TE Part # 179593-2
POWER D/LOCK REC CONT. H/P L/P



TE Part # 5-179851-6
AMP POWER D/LOCK TAB HDR 2P V




TE Part # 9-179844-6
POWER D/LOCK HDR ASSY 2P /7.92



TE Part # 368571-6
PDL 3P PLUG 3.96(GWT) BLU



TE Part # 179839-6
AMP POWER D/LOCK T/HDR ASSY 3P



TE Part # 179844-6
AMP POWER D/LOCK T/HDR ASSY 2P



TE Part # CAT-P87024-R2435
Power Double Lock Receptacle


Also in the Series | Power Double Lock



Connector Contacts(24)



Connector Hardware(14)



PCB Headers & Receptacles(43)



Power Contacts(24)



Rectangular Connector Housings(240)




Rectangular Power Connectors(283)




Standard Rectangular Connectors(240)


Customers Also Bought




TE Part #179970-1
250 HSG. PL EX REC.



TE Part #170329-1
250 PL MKII REC. 15-10AWG TPBR



TE Part #170183-2
250 FASTON,REC.,22-18 AWG,TPBR



TE Part #177627-1
PL .250 (6.3 MM) HOUSING RECEPTACLE



TE Part #177917-1
AMP POWER DBL LOCK TAB (L)

TE Part #1-176497-1
250 HSG. PL EX FLAG REC. NAT

TE Part #173974-1
187 HSG. PL MKII REC. NAT

TE Part #170224-2
250 FASTON,REC.,16-10 AWG,BR

TE Part #170325-1
187 PL MKII REC. 20-16AWG PTBR

TE Part #41802
250 FASTON FLAG REC 18-12 AWG TPBR

Documents

Product Drawings

POWER DBL LOCK PLUG HSG 3P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_177899-6_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_177899-6_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_177899-6_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)



English

AMP POWER DOUBLELOCK CONNECTOR SERIES

English

Agency Approvals

UL

English