

# Product datasheet

Specifications




## TeSys GY - modular dual tariff contactor - 63 A - 4 NO - coil 220...240 V AC

Local distributor code:

395511301

GY6340M5

 **Discontinued on:** 9 Feb 2023

 **Discontinued**

**EAN Code:** 3389110643053

### Main

Range	TeSys
product name	TeSys GY
Product or component type	Modular dual tariff contactor
Device short name	GY63
Contactor application	Lighting Motor control Heating

### Complementary

Utilisation category	AC-7A AC-7B
Poles description	4P
power pole contact composition	4 NO
[Ue] rated operational voltage	<= 250 V AC
[Ie] rated operational current	63 A AC-7A 25 A AC-7B
Operating position	30°/vertical
Control circuit type	AC at 50 Hz
[Uc] control circuit voltage	220...240 V AC 50 Hz
[Uimp] rated impulse withstand voltage	4 kV
[Ith] conventional free air thermal current	63 A (at 50 °C) for power circuit
Irms rated making capacity	200 A at 400 V AC for power circuit conforming to IEC 61095
Rated breaking capacity	200 A at 400 V for power circuit conforming to IEC 61095
[Icw] rated short-time withstand current	504 A 40 °C - 10 s for power circuit 157 A 40 °C - 30 s for power circuit
Associated fuse rating	63 A gL at <= 440 V for power circuit
Average impedance	2 mOhm - Ith 63 A 50 Hz for power circuit
[Ui] rated insulation voltage	500 V conforming to IEC 61095 500 V conforming to VDE 0110
Electrical durability	AC-7A: 100000 cycles AC-7B: 100000 cycles
Power dissipation per pole	8 W
Control type	Remote control

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting mode	Clip-on
Mounting support	DIN rail
Standards	IEC 60947-5 IEC 61095
Connections - terminals	Control circuit: screw clamp terminals 1 cable(s) 2.5 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 2.5 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 2.5 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1.5 mm²solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm²solid without cable end Power circuit: screw clamp terminals 1 cable(s) 25 mm²flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 16 mm²flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 16 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 4 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 25 mm²solid without cable end Power circuit: screw clamp terminals 2 cable(s) 6 mm²solid without cable end
Tightening torque	Power circuit: 3.5 N.m - on screw clamp terminals Control circuit: 3.5 N.m - on screw clamp terminals
Operating time	10...25 ms opening 10...30 ms closing
Mechanical durability	1000000 cycles
Maximum operating rate	300 cyc/h 50 °C
Control circuit voltage limits	Drop-out: 0.2...0.75 Uc at 50 Hz (at <50 °C) Operational: 0.85...1.1 Uc at 50 Hz (at <50 °C)
Inrush power in VA	53 VA 50 Hz (at 20 °C)
Hold-in power consumption in VA	6.5 VA 50 Hz (at 20 °C)
Heat dissipation	2.1 W at 50/60 Hz

## Environment

IP degree of protection	IP40 conforming to VDE 0106 (in enclosure) IP20 conforming to VDE 0106
Protective treatment	TC
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C
Operating altitude	<= 3000 m
Mechanical robustness	Shocks contactor open: 10 Gn for 11 ms Shocks contactor closed: 15 Gn for 11 ms Vibrations contactor open: 2 Gn, 5...300 Hz Vibrations contactor closed: 3 Gn, 5...300 Hz
Total number of 18 mm modules	3
Height	85 mm
Width	54 mm
Depth	62.5 mm
Net weight	0.39 kg
Quantity per set	Set of 4
Colour	White

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	8.000 cm
Package 1 Width	9.500 cm
Package 1 Length	23.000 cm
Package 1 Weight	324.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	2.900 cm
Package 2 Width	30.000 cm
Package 2 Length	20.000 cm
Package 2 Weight	1.351 kg
Unit Type of Package 3	S03
Number of Units in Package 3	32
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	11.430 kg

## Logistical informations

Country of origin	FR
-------------------	----

## Contractual warranty


Warranty	18 months
----------	-----------

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.



[Environmental Data explained](#) >

[How we assess product sustainability](#) >

Use Better

 Materials and Substances	
Recycled metal content at CR level	0
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
<a href="#">EU RoHS Directive</a>	Compliant
SCIP Number	361e1245-bdfb-4c55-bca5-ee0430c46917

Use Again

 Repack and remanufacture	
Take-back	No
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins