

TRICOTRIL® K SPEZIAL 838



APPLICATION:

- Handling of contaminated heavy parts
- Cleaning and maintenance in chemical plants
- Galvanising works
- Petrochemistry
- Chemical industry

QUALITIES AND ADVANTAGES:

- Broad chemical resistance
- High mechanical resistance
- Good grip when handling greasy and oily parts
- High user comfort for long working periods without operator fatigue
- Skin friendly due to solvent-free adhesive on the cotton liner

FEATURES:

- AQL < 0,65
- Free from natural latex
- Cotton liner is fixed later to the finished glove, to ensure maximum protection
- Good cut resistance by para-aramid liner
- Food safety according to EU 1935/2004

ATTRIBUTE	DESCRIPTION / VALUES
Article No. Name	• 838 • Tricotril® K Spezial 838
Material	• Nitrile • Para-aramid
Description	• Seamless para-aramid liner, • Cuff, fully coated, • Palm profile
Length (mm)	• 350
Total thickness (mm)	• 1,7 ± 0,1
Coating thickness (mm)	• 0,4
Colour	• Green
Size	• 9, 10, 11
Classification	• Category III EN 388:2016 3X42C EN 374-1/Type A AJKLOPT EN 374-5 Virus



CHEMICAL PROTECTIVE GLOVES

HONEYWELL PPE KCL GmbH

Industriepark Rhoen
Am Kreuzacker 9
36124 Eichenzell, Germany
Phone: +49 69 80885425
kclorders@honeywell.com
sps.honeywell.com

Honeywell KCL Tricotril Data Sheet - 01/2023
© 2023 Honeywell International Inc.

Honeywell

